

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264365

Luminaire Tested: **LD2B15D010 EU2B1510SP159035 2LBSQC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264365  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B15D010 EU2B1510SP159035 2LBSQC\*MW  
Description: 1500 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 984.0 lumens  
Efficiency: N/A  
Efficacy: 68.8 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264365

CATALOG NUMBER: LD2B15D010 EU2B1510SP159035 2LBSQC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P264365

CATALOG NUMBER: LD2B15D010 EU2B1510SP159035 2LBSQC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100																
	1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	98	98	98	98	98	98	98	98	98	98	98	98															
	2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	96	96	96	96	96	96	96	96	96	96	96	96															
	3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94	94	94	94	94	94	94	94	94	94	94	94	94															
	4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92	92	92	92	92	92	92	92	92	92	92	92	92															
	5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90	90	90	90	90	90	90	90	90	90	90	90	90															
	6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89	89	89	89	89	89	89	89	89	89	89	89	89															
	7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87	87	87	87	87	87	87	87	87	87	87	87	87															
	8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86	86	86	86	86	86	86	86	86	86	86	86	86															
	9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85	85	85	85	85	85	85	85	85	85	85	85	85															
	10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83	83	83	83	83	83	83	83	83	83	83	83	83															

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	4643126
5°	3721677
10°	1624354
15°	503360
20°	175463
25°	77518
30°	35093
35°	18249
40°	10433
45°	4954
50°	3070
55°	1720
60°	987
65°	1167
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264365

CATALOG NUMBER: LD2B15D010 EU2B1510SP159035 2LBSQC\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	570.7	58.0
10°-20°	312.5	31.8
20°-30°	71.2	7.2
30°-40°	20.5	2.1
40°-50°	6.3	0.6
50°-60°	1.9	0.2
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	954.4	97.0
0°-40°	974.9	99.1
0°-60°	983.1	99.9
0°-90°	984.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	984.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9411	
5°	7515	571
15°	986	313
25°	142	71
35°	30	20
45°	7	6
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264365

CATALOG NUMBER: LD2B15D010 EU2B1510SP159035 2LBSQC\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9411.2
1°	9294.0
2°	9050.7
3°	8673.0
4°	8154.0
5°	7514.8
6°	6731.2
7°	5855.7
8°	4941.9
9°	4057.3
10°	3242.4
11°	2552.7
12°	2009.5
13°	1581.3
14°	1249.1
15°	985.5
16°	777.5
17°	619.0
18°	497.8
19°	404.9
20°	334.2
22.5°	216.1
25°	142.4
26°	120.2
27°	102.0
28°	85.8
29°	71.7
30°	61.6
32.5°	42.4
35°	30.3
37.5°	22.2
40°	16.2
42.5°	11.1
45°	7.1
47.5°	5.0
50°	4.0
52.5°	3.0
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0



TEST NUMBER: P264365

CATALOG NUMBER: LD2B15D010 EU2B1510SP159035 2LBSQC\*MW

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)