

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264406

Luminaire Tested: **LD2B15D010 EU2B1510SP159040 2LBD*LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159040 2LBD*LI
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1108.9 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264406

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBD*LI

Luminous Intensity Polar Plot





TEST NUMBER: P264406

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBD*LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98	98	97	96						98										
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96	95						96												
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94						94													
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92						92													
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90						90													
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89						89													
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87						87													
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86						86													
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85						85													
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83						83													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5232940
5°	4194439
10°	1830704
15°	567307
20°	197777
25°	87371
30°	39536
35°	20538
40°	11721
45°	5582
50°	3531
55°	1978
60°	1085
65°	1284
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264406

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBD*LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	643.2	58.0
10°-20°	352.2	31.8
20°-30°	80.3	7.2
30°-40°	23.1	2.1
40°-50°	7.1	0.6
50°-60°	2.1	0.2
60°-70°	1.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.7	97.0
0°-40°	1098.7	99.1
0°-60°	1108.0	99.9
0°-90°	1108.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1108.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10607	
5°	8469	643
15°	1111	352
25°	160	80
35°	34	23
45°	8	7
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264406

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBD*LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10606.7
1°	10474.7
2°	10200.4
3°	9774.8
4°	9189.8
5°	8469.4
6°	7586.3
7°	6599.6
8°	5569.7
9°	4572.7
10°	3654.3
11°	2877.0
12°	2264.7
13°	1782.2
14°	1407.8
15°	1110.7
16°	876.3
17°	697.6
18°	561.1
19°	456.4
20°	376.7
22.5°	243.5
25°	160.5
26°	135.4
27°	114.9
28°	96.7
29°	80.8
30°	69.4
32.5°	47.8
35°	34.1
37.5°	25.0
40°	18.2
42.5°	12.5
45°	8.0
47.5°	5.7
50°	4.6
52.5°	3.4
55°	2.3
57.5°	1.1
60°	1.1
62.5°	1.1
65°	1.1
67.5°	1.1



TEST NUMBER: P264406

CATALOG NUMBER: LD2B15D010 EU2B1510SP159040 2LBD*LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)