

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P263920

Luminaire Tested: **LD2B05D010 EU2B0510SP158027 2LBDC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P263920
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B0510SP158027 2LBDC*MW
Description: 500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 709.0 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P263920

CATALOG NUMBER: LD2B05D010 EU2B0510SP158027 2LBDC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P263920

CATALOG NUMBER: LD2B05D010 EU2B0510SP158027 2LBDC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98				98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96				96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94				94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92				92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90				90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89				89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87				87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86				86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85				85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83				83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3345486
5°	2681561
10°	1170372
15°	362695
20°	126426
25°	55852
30°	25294
35°	13130
40°	7471
45°	3558
50°	2226
55°	1290
60°	691
65°	817
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P263920

CATALOG NUMBER: LD2B05D010 EU2B0510SP158027 2LBDC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	411.2	58.0
10°-20°	225.2	31.8
20°-30°	51.3	7.2
30°-40°	14.8	2.1
40°-50°	4.5	0.6
50°-60°	1.4	0.2
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.7	97.0
0°-40°	702.4	99.1
0°-60°	708.4	99.9
0°-90°	709.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	709.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6781	
5°	5415	411
15°	710	225
25°	103	51
35°	22	15
45°	5	5
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P263920

CATALOG NUMBER: LD2B05D010 EU2B0510SP158027 2LBDC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6781.0
1°	6696.6
2°	6521.3
3°	6249.2
4°	5875.2
5°	5414.6
6°	4850.0
7°	4219.2
8°	3560.8
9°	2923.4
10°	2336.2
11°	1839.3
12°	1447.9
13°	1139.4
14°	900.0
15°	710.1
16°	560.2
17°	446.0
18°	358.7
19°	291.8
20°	240.8
22.5°	155.7
25°	102.6
26°	86.6
27°	73.5
28°	61.8
29°	51.7
30°	44.4
32.5°	30.6
35°	21.8
37.5°	16.0
40°	11.6
42.5°	8.0
45°	5.1
47.5°	3.6
50°	2.9
52.5°	2.2
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7



TEST NUMBER: P263920

CATALOG NUMBER: LD2B05D010 EU2B0510SP158027 2LBDC*MW

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)