

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265143

Luminaire Tested: **LD2B15D010 EU2B1510SP159050 2LBLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265143
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B1510SP159050 2LBLC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1096.0 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265143

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P265143

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|--|--|--|--|--|----|--|--|--|--|--|--|--|--|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 | | | | | | | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | |
| RCR | 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | 100 | | | | | | | | | | | | | | | |
| | 1 | 115 | 113 | 111 | 110 | 113 | 111 | 110 | 108 | 107 | 106 | 105 | 104 | 103 | 102 | 100 | 99 | 99 | 97 | 97 | 97 | 97 | 97 | 97 | 97 | 97 | 97 | 97 | 97 | 97 | | | | | | | | | | | | | | | |
| | 2 | 112 | 108 | 106 | 103 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99 | 98 | 98 | 97 | 96 | 94 | 94 | 94 | 94 | 94 | 94 | 94 | 94 | 94 | 94 | 94 | 94 | | | | | | | | | | | | | | | |
| | 3 | 109 | 104 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 98 | 96 | 98 | 96 | 94 | 96 | 94 | 93 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | 92 | | | | | | | | | | | | | | | |
| | 4 | 105 | 100 | 97 | 94 | 104 | 99 | 96 | 93 | 97 | 95 | 92 | 96 | 93 | 91 | 94 | 92 | 90 | 89 | 89 | 89 | 89 | 89 | 89 | 89 | 89 | 89 | 89 | 89 | 89 | | | | | | | | | | | | | | | |
| | 5 | 103 | 97 | 93 | 91 | 101 | 96 | 93 | 90 | 95 | 92 | 89 | 93 | 91 | 89 | 92 | 90 | 88 | 87 | 87 | 87 | 87 | 87 | 87 | 87 | 87 | 87 | 87 | 87 | 87 | | | | | | | | | | | | | | | |
| | 6 | 100 | 94 | 90 | 88 | 99 | 94 | 90 | 87 | 92 | 89 | 87 | 91 | 88 | 86 | 90 | 88 | 86 | 85 | 85 | 85 | 85 | 85 | 85 | 85 | 85 | 85 | 85 | 85 | 85 | | | | | | | | | | | | | | | |
| | 7 | 98 | 92 | 88 | 85 | 97 | 91 | 88 | 85 | 90 | 87 | 85 | 89 | 86 | 84 | 88 | 86 | 84 | 83 | 83 | 83 | 83 | 83 | 83 | 83 | 83 | 83 | 83 | 83 | 83 | 83 | | | | | | | | | | | | | | |
| | 8 | 95 | 89 | 86 | 83 | 94 | 89 | 85 | 83 | 88 | 85 | 82 | 87 | 84 | 82 | 86 | 84 | 82 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | 81 | | | | | | | | | | | | | | |
| | 9 | 93 | 87 | 83 | 81 | 92 | 87 | 83 | 81 | 86 | 83 | 81 | 85 | 82 | 80 | 85 | 82 | 80 | 79 | 79 | 79 | 79 | 79 | 79 | 79 | 79 | 79 | 79 | 79 | 79 | 79 | | | | | | | | | | | | | | |
| | 10 | 91 | 85 | 82 | 79 | 91 | 85 | 81 | 79 | 84 | 81 | 79 | 84 | 81 | 79 | 83 | 80 | 78 | 78 | 78 | 78 | 78 | 78 | 78 | 78 | 78 | 78 | 78 | 78 | 78 | 78 | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 3869091 |
| 5° | 3149073 |
| 10° | 1701053 |
| 15° | 678246 |
| 20° | 271963 |
| 25° | 130212 |
| 30° | 67508 |
| 35° | 35715 |
| 40° | 19772 |
| 45° | 12280 |
| 50° | 8443 |
| 55° | 5677 |
| 60° | 4342 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P265143

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBLC*MMS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 511.4 | 46.7 |
| 10°-20° | 403.5 | 36.8 |
| 20°-30° | 119.0 | 10.9 |
| 30°-40° | 39.6 | 3.6 |
| 40°-50° | 14.9 | 1.4 |
| 50°-60° | 6.6 | 0.6 |
| 60°-70° | 1.1 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1033.8 | 94.3 |
| 0°-40° | 1073.4 | 97.9 |
| 0°-60° | 1095.0 | 99.9 |
| 0°-90° | 1096.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1096.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 7842 | |
| 5° | 6359 | 511 |
| 15° | 1328 | 403 |
| 25° | 239 | 119 |
| 35° | 59 | 40 |
| 45° | 18 | 15 |
| 55° | 7 | 7 |
| 65° | 0 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P265143

CATALOG NUMBER: LD2B15D010 EU2B1510SP159050 2LBLC*MMS

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 7842.3 |
| 2.5° | 7526.3 |
| 5° | 6358.6 |
| 7.5° | 4899.0 |
| 10° | 3395.5 |
| 12.5° | 2172.9 |
| 15° | 1327.9 |
| 17.5° | 809.9 |
| 20° | 518.0 |
| 22.5° | 346.8 |
| 25° | 239.2 |
| 27.5° | 169.0 |
| 30° | 118.5 |
| 32.5° | 83.4 |
| 35° | 59.3 |
| 37.5° | 41.7 |
| 40° | 30.7 |
| 42.5° | 24.1 |
| 45° | 17.6 |
| 47.5° | 15.4 |
| 50° | 11.0 |
| 52.5° | 8.8 |
| 55° | 6.6 |
| 57.5° | 6.6 |
| 60° | 4.4 |
| 62.5° | 2.2 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)