

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225307

Luminaire Tested: **LD2B15D010 EU2B15FL409030D2W 2LBDC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225307
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15FL409030D2W 2LBDC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 825.0 lumens
Efficiency: N/A
Efficacy: 57.7 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225307

CATALOG NUMBER: LD2B15D010 EU2B15FL409030D2W 2LBDC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P225307

CATALOG NUMBER: LD2B15D010 EU2B15FL409030D2W 2LBDC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																											
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91																											
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86																											
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82																											
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79																											
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75																											
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72																											
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69																											
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66																											
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	747035
5°	733403
10°	651970
15°	512772
20°	341223
25°	195872
30°	98936
35°	46530
40°	18759
45°	9258
50°	5062
55°	3579
60°	3254
65°	1925
70°	2378
75°	1497
80°	2231
85°	0



TEST NUMBER: P225307

CATALOG NUMBER: LD2B15D010 EU2B15FL409030D2W 2LBDC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	20.9
10°-20°	346.4	42.0
20°-30°	215.5	26.1
30°-40°	66.2	8.0
40°-50°	14.5	1.8
50°-60°	5.2	0.6
60°-70°	2.6	0.3
70°-80°	1.5	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	734.6	89.0
0°-40°	800.8	97.1
0°-60°	820.5	99.5
0°-90°	825.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	825.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1929	
5°	1886	173
15°	1279	346
25°	458	215
35°	98	66
45°	17	15
55°	5	5
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P225307

CATALOG NUMBER: LD2B15D010 EU2B15FL409030D2W 2LBDC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1928.6
2.5°	1920.1
5°	1886.2
7.5°	1800.5
10°	1657.6
12.5°	1486.1
15°	1278.7
17.5°	1052.2
20°	827.8
22.5°	627.7
25°	458.3
27.5°	322.8
30°	221.2
32.5°	149.2
35°	98.4
37.5°	59.3
40°	37.1
42.5°	25.4
45°	16.9
47.5°	11.6
50°	8.4
52.5°	7.4
55°	5.3
57.5°	4.2
60°	4.2
62.5°	3.2
65°	2.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	1.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)