

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P222756

Luminaire Tested: **LD2B15D010 EU2B15NFL259030D2W 2LBDSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P222756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (155)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B15D010 EU2B15NFL259030D2W 2LBDSQC*MMS
Description: 1500 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 778.7 lumens
Efficiency: N/A
Efficacy: 54.5 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P222756

CATALOG NUMBER: LD2B15D010 EU2B15NFL259030D2W 2LBDSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P222756

CATALOG NUMBER: LD2B15D010 EU2B15NFL259030D2W 2LBDSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97						97													
2	112	109	106	104	110	107	104	102	104	102	100	101	99	98	98	97	96	95						95													
3	109	105	101	99	107	103	100	98	101	98	96	99	97	95	96	95	93	92						92													
4	106	101	97	95	104	100	97	94	98	95	93	96	94	92	95	93	91	90						90													
5	103	98	94	91	102	97	94	91	95	92	90	94	91	89	93	90	89	88						88													
6	101	95	91	89	99	94	91	88	93	90	88	92	89	87	91	88	87	86						86													
7	98	92	89	86	97	92	88	86	91	88	85	90	87	85	89	87	85	84						84													
8	96	90	86	84	95	90	86	84	89	86	83	88	85	83	87	85	83	82						82													
9	94	88	84	82	93	88	84	82	87	84	82	86	83	81	85	83	81	80						80													
10	92	86	82	80	91	86	82	80	85	82	80	84	82	80	84	81	79	79						79													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1789422
5°	1652237
10°	1118331
15°	380478
20°	139737
25°	74109
30°	38107
35°	17780
40°	5815
45°	2958
50°	1386
55°	473
60°	542
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P222756

CATALOG NUMBER: LD2B15D010 EU2B15NFL259030D2W 2LBDSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	361.5	46.4
10°-20°	303.9	39.0
20°-30°	83.4	10.7
30°-40°	24.3	3.1
40°-50°	4.5	0.6
50°-60°	1.0	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	748.8	96.2
0°-40°	773.1	99.3
0°-60°	778.6	100.0
0°-90°	778.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	778.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4620	
5°	4249	361
15°	949	304
25°	173	83
35°	38	24
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P222756

CATALOG NUMBER: LD2B15D010 EU2B15NFL259030D2W 2LBDSQC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	4619.7
1°	4592.9
2°	4545.3
3°	4477.1
4°	4383.5
5°	4249.3
6°	4066.0
7°	3836.6
8°	3556.7
9°	3226.1
10°	2843.3
11°	2423.8
12°	1987.4
13°	1570.9
14°	1215.7
15°	948.8
17.5°	535.4
20°	339.0
22.5°	241.6
25°	173.4
27.5°	122.8
30°	85.2
32.5°	59.9
35°	37.6
37.5°	15.3
40°	11.5
42.5°	8.4
45°	5.4
47.5°	3.0
50°	2.3
52.5°	1.6
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P222756

CATALOG NUMBER: LD2B15D010 EU2B15NFL259030D2W 2LBDSQC*MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)