

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264392

Luminaire Tested: **LD2B05D010 EU2B0510SP159040 2LBSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B0510SP159040 2LBSQC*MMS
Description: 500 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 644.0 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264392

CATALOG NUMBER: LD2B05D010 EU2B0510SP159040 2LBSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P264392

CATALOG NUMBER: LD2B05D010 EU2B0510SP159040 2LBSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 100 | 98 | | | 98 |
| 2 | 113 | 109 | 107 | 105 | 111 | 108 | 106 | 104 | 105 | 103 | 101 | 102 | 101 | 99 | 99 | 98 | 97 | 96 | | | 96 |
| 3 | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 100 | 102 | 100 | 98 | 100 | 98 | 97 | 98 | 96 | 95 | 94 | | | 94 |
| 4 | 107 | 103 | 99 | 97 | 106 | 102 | 99 | 96 | 100 | 97 | 95 | 98 | 96 | 94 | 96 | 95 | 93 | 92 | | | 92 |
| 5 | 105 | 100 | 97 | 94 | 104 | 99 | 96 | 94 | 98 | 95 | 93 | 96 | 94 | 92 | 95 | 93 | 91 | 90 | | | 90 |
| 6 | 103 | 98 | 94 | 92 | 102 | 97 | 94 | 91 | 96 | 93 | 91 | 95 | 92 | 90 | 93 | 91 | 90 | 89 | | | 89 |
| 7 | 101 | 95 | 92 | 90 | 100 | 95 | 92 | 89 | 94 | 91 | 89 | 93 | 90 | 89 | 92 | 90 | 88 | 87 | | | 87 |
| 8 | 99 | 93 | 90 | 88 | 98 | 93 | 90 | 88 | 92 | 89 | 87 | 91 | 89 | 87 | 91 | 88 | 87 | 86 | | | 86 |
| 9 | 97 | 92 | 88 | 86 | 96 | 91 | 88 | 86 | 91 | 88 | 86 | 90 | 87 | 86 | 89 | 87 | 85 | 85 | | | 85 |
| 10 | 95 | 90 | 87 | 85 | 95 | 90 | 87 | 85 | 89 | 86 | 85 | 89 | 86 | 84 | 88 | 86 | 84 | 83 | | | 83 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 3038763 |
| 5° | 2435721 |
| 10° | 1063114 |
| 15° | 329444 |
| 20° | 114823 |
| 25° | 50735 |
| 30° | 22958 |
| 35° | 11925 |
| 40° | 6827 |
| 45° | 3210 |
| 50° | 1996 |
| 55° | 1118 |
| 60° | 691 |
| 65° | 817 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P264392

CATALOG NUMBER: LD2B05D010 EU2B0510SP159040 2LBSQC*MMS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 373.5 | 58.0 |
| 10°-20° | 204.5 | 31.8 |
| 20°-30° | 46.6 | 7.2 |
| 30°-40° | 13.4 | 2.1 |
| 40°-50° | 4.1 | 0.6 |
| 50°-60° | 1.2 | 0.2 |
| 60°-70° | 0.6 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 624.6 | 97.0 |
| 0°-40° | 638.0 | 99.1 |
| 0°-60° | 643.4 | 99.9 |
| 0°-90° | 644.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 644.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 6159 | |
| 5° | 4918 | 373 |
| 15° | 645 | 205 |
| 25° | 93 | 47 |
| 35° | 20 | 13 |
| 45° | 5 | 4 |
| 55° | 1 | 1 |
| 65° | 1 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P264392

CATALOG NUMBER: LD2B05D010 EU2B0510SP159040 2LBSQC*MMS

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 6159.3 |
| 1° | 6082.7 |
| 2° | 5923.4 |
| 3° | 5676.2 |
| 4° | 5336.6 |
| 5° | 4918.2 |
| 6° | 4405.4 |
| 7° | 3832.4 |
| 8° | 3234.3 |
| 9° | 2655.4 |
| 10° | 2122.1 |
| 11° | 1670.7 |
| 12° | 1315.1 |
| 13° | 1034.9 |
| 14° | 817.5 |
| 15° | 645.0 |
| 16° | 508.9 |
| 17° | 405.1 |
| 18° | 325.8 |
| 19° | 265.0 |
| 20° | 218.7 |
| 22.5° | 141.4 |
| 25° | 93.2 |
| 26° | 78.6 |
| 27° | 66.7 |
| 28° | 56.2 |
| 29° | 46.9 |
| 30° | 40.3 |
| 32.5° | 27.8 |
| 35° | 19.8 |
| 37.5° | 14.5 |
| 40° | 10.6 |
| 42.5° | 7.3 |
| 45° | 4.6 |
| 47.5° | 3.3 |
| 50° | 2.6 |
| 52.5° | 2.0 |
| 55° | 1.3 |
| 57.5° | 0.7 |
| 60° | 0.7 |
| 62.5° | 0.7 |
| 65° | 0.7 |
| 67.5° | 0.7 |



TEST NUMBER: P264392

CATALOG NUMBER: LD2B05D010 EU2B0510SP159040 2LBSQC*MMS

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 70° | | 0.0 |
| 72.5° | | 0.0 |



(END OF REPORT)