

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264632

Luminaire Tested: **LD2B20D010 EU2B2010SP158027 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264632
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP158027 2LBDL*WMH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1626.0 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264632

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P264632

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97						97													
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94						94													
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92						92													
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89						89													
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87						87													
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85						85													
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83						83													
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81						81													
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79						79													
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78						78													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5740116
5°	4671857
10°	2523650
15°	1006208
20°	403481
25°	193195
30°	100151
35°	52941
40°	29368
45°	18210
50°	12511
55°	8429
60°	6414
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264632

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	758.6	46.7
10°-20°	598.6	36.8
20°-30°	176.6	10.9
30°-40°	58.8	3.6
40°-50°	22.1	1.4
50°-60°	9.8	0.6
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1533.8	94.3
0°-40°	1592.5	97.9
0°-60°	1624.4	99.9
0°-90°	1626.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1626.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11635	
5°	9433	759
15°	1970	599
25°	355	177
35°	88	59
45°	26	22
55°	10	10
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264632

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	11634.7
2.5°	11165.8
5°	9433.4
7.5°	7268.0
10°	5037.5
12.5°	3223.7
15°	1970.0
17.5°	1201.6
20°	768.5
22.5°	514.5
25°	354.9
27.5°	250.7
30°	175.8
32.5°	123.7
35°	87.9
37.5°	61.9
40°	45.6
42.5°	35.8
45°	26.1
47.5°	22.8
50°	16.3
52.5°	13.0
55°	9.8
57.5°	9.8
60°	6.5
62.5°	3.3
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)