

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223891

Luminaire Tested: **LD2B05D010 EU2B05SP159027 2LBDC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P223891  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA ( 150)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B05D010 EU2B05SP159027 2LBDC\*MMS  
Description: 500 Lumen, 2inch Portfolio LED Downlight  
SPOT OPTIC  
CAST ROUND TRIM WITH MATTE METALLIC SILVER  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 344.0 lumens  
Efficiency: N/A  
Efficacy: 47.1 lumens/watt  
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P223891

CATALOG NUMBER: LD2B05D010 EU2B05SP159027 2LBDC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P223891

CATALOG NUMBER: LD2B05D010 EU2B05SP159027 2LBDC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98									98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96									96																			
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94									94																			
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93									93																			
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91									91																			
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90									90																			
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88									88																			
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	89	88	87									87																			
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86									86																			
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85									85																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1652999
5°	1194939
10°	347893
15°	122067
20°	52268
25°	23506
30°	9080
35°	4539
40°	3034
45°	1972
50°	1085
55°	810
60°	465
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223891

CATALOG NUMBER: LD2B05D010 EU2B05SP159027 2LBDC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	217.5	63.2
10°-20°	88.5	25.7
20°-30°	27.2	7.9
30°-40°	6.7	2.0
40°-50°	2.8	0.8
50°-60°	1.2	0.3
60°-70°	0.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	333.1	96.8
0°-40°	339.8	98.8
0°-60°	343.8	99.9
0°-90°	344.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	344.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4268	
5°	3073	217
15°	304	88
25°	55	27
35°	10	7
45°	4	3
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223891

CATALOG NUMBER: LD2B05D010 EU2B05SP159027 2LBDC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4267.5
1°	4202.3
2°	4043.2
3°	3789.7
4°	3458.4
5°	3073.2
6°	2639.1
7°	2167.8
8°	1690.0
9°	1243.3
10°	884.5
11°	633.9
12°	476.6
13°	388.1
14°	339.7
15°	304.4
17.5°	187.8
20°	126.8
22.5°	84.9
25°	55.0
27.5°	33.5
30°	20.3
32.5°	13.2
35°	9.6
37.5°	7.8
40°	6.0
42.5°	4.8
45°	3.6
47.5°	2.4
50°	1.8
52.5°	1.8
55°	1.2
57.5°	1.2
60°	0.6
62.5°	0.6
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223891

CATALOG NUMBER: LD2B05D010 EU2B05SP159027 2LBDC\*MMS

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)