

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P263962

Luminaire Tested: **LD2B20D010 EU2B2010SP158027 2LBSQC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P263962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP158027 2LBSQC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1554.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P263962

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBSQC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P263962

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBSQC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98			98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96			96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94			94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92			92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90			90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89			89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87			87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86			86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85			85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83			83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7332738
5°	5877534
10°	2565281
15°	794956
20°	277161
25°	122428
30°	55430
35°	28789
40°	16423
45°	7814
50°	4912
55°	2752
60°	1579
65°	1868
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P263962

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBSQC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	901.2	58.0
10°-20°	493.6	31.8
20°-30°	112.5	7.2
30°-40°	32.3	2.1
40°-50°	10.0	0.6
50°-60°	3.0	0.2
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1507.3	97.0
0°-40°	1539.7	99.1
0°-60°	1552.6	99.9
0°-90°	1554.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1554.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14863	
5°	11868	901
15°	1556	494
25°	225	113
35°	48	32
45°	11	10
55°	3	3
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P263962

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBSQC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	14862.8
1°	14677.8
2°	14293.5
3°	13697.0
4°	12877.3
5°	11867.9
6°	10630.4
7°	9247.8
8°	7804.5
9°	6407.6
10°	5120.6
11°	4031.4
12°	3173.5
13°	2497.3
14°	1972.7
15°	1556.4
16°	1227.9
17°	977.6
18°	786.2
19°	639.5
20°	527.9
22.5°	341.3
25°	224.9
26°	189.8
27°	161.1
28°	135.6
29°	113.2
30°	97.3
32.5°	67.0
35°	47.8
37.5°	35.1
40°	25.5
42.5°	17.5
45°	11.2
47.5°	8.0
50°	6.4
52.5°	4.8
55°	3.2
57.5°	1.6
60°	1.6
62.5°	1.6
65°	1.6
67.5°	1.6



TEST NUMBER: P263962

CATALOG NUMBER: LD2B20D010 EU2B2010SP158027 2LBSQC*MW

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)