

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B05D010 EU2B0510NFL258030 2LBPINW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14816)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B0510NFL258030 2LBPINW
Description: 500 Lumen, 2inch Portfolio LED Downlight
NARROW FLOOD OPTIC
ROUND PINHOLE WHITE OCULUS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 634.0 lumens
Efficiency: N/A
Efficacy: 86.8 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B0510NFL258030 2LBPINW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B0510NFL258030 2LBPINW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	97
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	95
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95	94	94	93
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	92	92	90
4	106	101	98	95	105	100	97	95	98	96	94	97	94	93	95	93	92	90	89	89	88
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	88	87	87	86
6	101	96	92	89	100	95	91	89	94	91	88	92	90	88	91	89	87	86	85	85	85
7	99	93	89	87	98	93	89	87	92	88	86	91	88	86	90	87	85	84	84	84	83
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	86	84	82	82	82	81
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	80	80	80	80
10	93	87	83	81	92	87	83	81	86	83	81	85	83	81	85	82	80	80	80	80	80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1488680
5°	1382461
10°	939629
15°	310855
20°	105604
25°	53486
30°	27606
35°	9082
40°	3389
45°	1808
50°	482
55°	540
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B0510NFL258030 2LBPINW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.9	47.6
10°-20°	252.2	39.8
20°-30°	61.0	9.6
30°-40°	15.8	2.5
40°-50°	2.6	0.4
50°-60°	0.4	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	615.2	97.0
0°-40°	630.9	99.5
0°-60°	634.0	100.0
0°-90°	634.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	634.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3842	
5°	3554	302
15°	775	252
25°	125	61
35°	19	16
45°	3	3
55°	1	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B0510NFL258030 2LBPINW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3841.9
2.5°	3777.7
5°	3554.2
7.5°	3091.2
10°	2388.1
12.5°	1477.2
15°	774.9
17.5°	418.7
20°	256.1
22.5°	176.8
25°	125.1
27.5°	88.4
30°	61.7
32.5°	43.4
35°	19.2
37.5°	8.3
40°	6.7
42.5°	5.0
45°	3.3
47.5°	1.7
50°	0.8
52.5°	0.8
55°	0.8
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)