

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224996

Luminaire Tested: **LD2B05D010 EU2B05FL408030 2LBDL\*LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224996  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (152)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B05D010 EU2B05FL408030 2LBDL\*LI  
Description: 500 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 725.0 lumens  
Efficiency: N/A  
Efficacy: 99.3 lumens/watt  
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.58  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224996

CATALOG NUMBER: LD2B05D010 EU2B05FL408030 2LBDL\*LI

### Luminous Intensity Polar Plot





TEST NUMBER: P224996

CATALOG NUMBER: LD2B05D010 EU2B05FL408030 2LBDL\*LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96			
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91			
3	106	101	96	93	104	99	95	92	97	94	91	94	92	90	92	90	88	87			
4	102	96	91	88	100	95	90	87	93	89	86	91	88	85	89	86	84	83			
5	98	91	86	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79			
6	94	87	82	79	93	86	82	79	85	81	78	84	80	78	83	79	77	76			
7	91	83	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73			
8	88	80	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	70			
9	85	77	72	69	84	76	72	69	76	71	69	75	71	68	74	71	68	67			
10	82	74	69	66	81	74	69	66	73	69	66	72	68	66	72	68	66	65			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	695480
5°	668313
10°	581762
15°	454304
20°	302146
25°	173007
30°	86010
35°	39531
40°	15877
45°	7231
50°	3375
55°	1891
60°	1085
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224996

CATALOG NUMBER: LD2B05D010 EU2B05FL408030 2LBDL\*LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	156.4	21.6
10°-20°	307.2	42.4
20°-30°	190.1	26.2
30°-40°	56.9	7.8
40°-50°	11.4	1.6
50°-60°	2.8	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	653.8	90.2
0°-40°	710.7	98.0
0°-60°	724.9	100.0
0°-90°	725.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	725.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1796	
5°	1719	156
15°	1133	307
25°	405	190
35°	84	57
45°	13	11
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224996

CATALOG NUMBER: LD2B05D010 EU2B05FL408030 2LBDL\*LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1795.5
1°	1785.7
2°	1776.6
3°	1758.5
4°	1741.8
5°	1718.8
6°	1687.5
7°	1647.8
8°	1596.9
9°	1539.1
10°	1479.1
11°	1417.1
12°	1350.9
13°	1282.0
14°	1208.1
15°	1132.9
17.5°	934.3
20°	733.0
22.5°	554.6
25°	404.8
27.5°	284.3
30°	192.3
32.5°	126.8
35°	83.6
37.5°	52.3
40°	31.4
42.5°	20.2
45°	13.2
47.5°	8.4
50°	5.6
52.5°	4.2
55°	2.8
57.5°	2.1
60°	1.4
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P224996

CATALOG NUMBER: LD2B05D010 EU2B05FL408030 2LBDL\*LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)