

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B20D010 EU2B2010NFL259040 2LBPINW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P#  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14816)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B2010NFL259040 2LBPINW  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
NARROW FLOOD OPTIC  
ROUND PINHOLE WHITE OCULUS  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1314.0 lumens  
Efficiency: N/A  
Efficacy: 62.9 lumens/watt  
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.35  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B2010NFL259040 2LBPINW

### Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B2010NFL259040 2LBPINW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93	93
4	106	101	98	95	105	100	97	95	98	96	94	97	94	93	95	93	92	90	90	90	90
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	89	88	88	88	88
6	101	96	92	89	100	95	91	89	94	91	88	92	90	88	91	89	87	86	86	86	86
7	99	93	89	87	98	93	89	87	92	88	86	91	88	86	90	87	85	85	85	85	85
8	97	91	87	85	96	90	87	85	90	86	84	89	86	84	88	85	84	83	83	83	83
9	95	89	85	83	94	88	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
10	93	87	83	81	92	87	83	81	86	83	81	85	83	81	85	82	80	80	80	80	80

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3085392
5°	2865198
10°	1947406
15°	644254
20°	218836
25°	110862
30°	57226
35°	18827
40°	6980
45°	3781
50°	1025
55°	1148
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B2010NFL259040 2LBPINW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	625.8	47.6
10°-20°	522.8	39.8
20°-30°	126.5	9.6
30°-40°	32.7	2.5
40°-50°	5.4	0.4
50°-60°	0.9	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1275.0	97.0
0°-40°	1307.6	99.5
0°-60°	1314.0	100.0
0°-90°	1314.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1314.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7963	
5°	7366	626
15°	1606	523
25°	259	126
35°	40	33
45°	7	5
55°	2	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B2010NFL259040 2LBPINW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7962.6
2.5°	7829.5
5°	7366.2
7.5°	6406.8
10°	4949.4
12.5°	3061.6
15°	1606.0
17.5°	867.8
20°	530.7
22.5°	366.5
25°	259.3
27.5°	183.2
30°	127.9
32.5°	89.9
35°	39.8
37.5°	17.3
40°	13.8
42.5°	10.4
45°	6.9
47.5°	3.5
50°	1.7
52.5°	1.7
55°	1.7
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)