

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224597

Luminaire Tested: **LD2B05D010 EU2B05FL409730 2LBDLC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224597
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14836)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05FL409730 2LBDLC*MMS
Description: 500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 526.0 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224597

CATALOG NUMBER: LD2B05D010 EU2B05FL409730 2LBDLC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224597

CATALOG NUMBER: LD2B05D010 EU2B05FL409730 2LBDLC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																												
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91																												
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87																												
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83																												
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	82	80	79																												
6	94	87	82	78	93	86	82	78	85	81	78	83	80	77	82	79	77	75																												
7	91	83	78	75	89	82	78	75	81	77	74	80	77	74	79	76	73	72																												
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69																												
9	84	76	72	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67																												
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	478798
5°	469585
10°	417157
15°	329189
20°	219582
25°	126379
30°	64004
35°	30027
40°	12287
45°	5533
50°	2832
55°	1823
60°	1085
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224597

CATALOG NUMBER: LD2B05D010 EU2B05FL409730 2LBDLC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.5	21.0
10°-20°	221.8	42.2
20°-30°	138.9	26.4
30°-40°	43.0	8.2
40°-50°	8.9	1.7
50°-60°	2.5	0.5
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	471.3	89.6
0°-40°	514.3	97.8
0°-60°	525.7	99.9
0°-90°	526.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	526.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1236	
5°	1208	111
15°	821	222
25°	296	139
35°	64	43
45°	10	9
55°	3	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224597

CATALOG NUMBER: LD2B05D010 EU2B05FL409730 2LBDLC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1236.1
2.5°	1230.0
5°	1207.7
7.5°	1151.0
10°	1060.6
12.5°	949.2
15°	820.9
17.5°	673.1
20°	532.7
22.5°	405.1
25°	295.7
27.5°	207.9
30°	143.1
32.5°	95.9
35°	63.5
37.5°	39.8
40°	24.3
42.5°	15.5
45°	10.1
47.5°	6.8
50°	4.7
52.5°	3.4
55°	2.7
57.5°	2.0
60°	1.4
62.5°	0.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)