

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224654

Luminaire Tested: **LD2B05D010 EU2B05FL409730 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224654
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05FL409730 2LBDLC*MW
Description: 500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 527.1 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224654

CATALOG NUMBER: LD2B05D010 EU2B05FL409730 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224654

CATALOG NUMBER: LD2B05D010 EU2B05FL409730 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91																
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86																
4	101	95	90	87	100	94	90	86	92	88	85	90	87	84	88	86	84	82			82																
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79																
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			75																
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72																
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69																
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66																
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	477094
5°	468418
10°	416409
15°	327465
20°	217892
25°	125097
30°	63199
35°	29743
40°	11984
45°	5916
50°	3254
55°	2296
60°	2092
65°	1283
70°	1586
75°	1048
80°	1561
85°	0



TEST NUMBER: P224654

CATALOG NUMBER: LD2B05D010 EU2B05FL409730 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.3	20.9
10°-20°	221.2	42.0
20°-30°	137.6	26.1
30°-40°	42.3	8.0
40°-50°	9.3	1.8
50°-60°	3.3	0.6
60°-70°	1.7	0.3
70°-80°	1.0	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	469.2	89.0
0°-40°	511.5	97.0
0°-60°	524.1	99.4
0°-90°	527.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	527.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1232	
5°	1205	110
15°	817	221
25°	293	138
35°	63	42
45°	11	9
55°	3	3
65°	1	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224654

CATALOG NUMBER: LD2B05D010 EU2B05FL409730 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1231.7
2.5°	1226.3
5°	1204.7
7.5°	1149.9
10°	1058.7
12.5°	949.1
15°	816.6
17.5°	672.0
20°	528.6
22.5°	400.9
25°	292.7
27.5°	206.2
30°	141.3
32.5°	95.3
35°	62.9
37.5°	37.9
40°	23.7
42.5°	16.2
45°	10.8
47.5°	7.4
50°	5.4
52.5°	4.7
55°	3.4
57.5°	2.7
60°	2.7
62.5°	2.0
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)