

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224755

Luminaire Tested: **LD2B05D010 EU2B05FL409035 2LBDL**MW***

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224755
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05FL409035 2LBDL*MW
Description: 500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 601.0 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224755

CATALOG NUMBER: LD2B05D010 EU2B05FL409035 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224755

CATALOG NUMBER: LD2B05D010 EU2B05FL409035 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																																				
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91																																				
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86																																				
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82																																				
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79																																				
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75																																				
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72																																				
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69																																				
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66																																				
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	544105
5°	534169
10°	474857
15°	373461
20°	248518
25°	142662
30°	72055
35°	33904
40°	13652
45°	6738
50°	3736
55°	2634
60°	2402
65°	1375
70°	1699
75°	1197
80°	1785
85°	0



TEST NUMBER: P224755

CATALOG NUMBER: LD2B05D010 EU2B05FL409035 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.8	20.9
10°-20°	252.3	42.0
20°-30°	156.9	26.1
30°-40°	48.3	8.0
40°-50°	10.6	1.8
50°-60°	3.8	0.6
60°-70°	1.9	0.3
70°-80°	1.1	0.2
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	535.0	89.0
0°-40°	583.3	97.1
0°-60°	597.7	99.4
0°-90°	601.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	601.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1405	
5°	1374	126
15°	931	252
25°	334	157
35°	72	48
45°	12	11
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224755

CATALOG NUMBER: LD2B05D010 EU2B05FL409035 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1404.7
2.5°	1398.5
5°	1373.8
7.5°	1311.4
10°	1207.3
12.5°	1082.4
15°	931.3
17.5°	766.3
20°	602.9
22.5°	457.2
25°	333.8
27.5°	235.1
30°	161.1
32.5°	108.7
35°	71.7
37.5°	43.2
40°	27.0
42.5°	18.5
45°	12.3
47.5°	8.5
50°	6.2
52.5°	5.4
55°	3.9
57.5°	3.1
60°	3.1
62.5°	2.3
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)