

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264013

Luminaire Tested: **LD2B20D010 EU2B2010SP158030 2LBSQC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264013
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP158030 2LBSQC*MB
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1728.0 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264013

CATALOG NUMBER: LD2B20D010 EU2B2010SP158030 2LBSQC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P264013

CATALOG NUMBER: LD2B20D010 EU2B2010SP158030 2LBSQC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98			98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96			96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94			94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92			92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90			90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89			89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87			87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86			86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85			85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83			83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8153741
5°	6535618
10°	2852538
15°	883982
20°	308189
25°	136091
30°	61640
35°	32041
40°	18291
45°	8652
50°	5449
55°	3011
60°	1776
65°	2101
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264013

CATALOG NUMBER: LD2B20D010 EU2B2010SP158030 2LBSQC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1002.1	58.0
10°-20°	548.8	31.8
20°-30°	125.1	7.2
30°-40°	36.0	2.1
40°-50°	11.1	0.6
50°-60°	3.3	0.2
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1676.1	97.0
0°-40°	1712.0	99.1
0°-60°	1726.5	99.9
0°-90°	1728.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1728.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16527	
5°	13197	###
15°	1731	549
25°	250	125
35°	53	36
45°	12	11
55°	4	3
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264013

CATALOG NUMBER: LD2B20D010 EU2B2010SP158030 2LBSQC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	16526.9
1°	16321.2
2°	15893.9
3°	15230.7
4°	14319.2
5°	13196.7
6°	11820.7
7°	10283.2
8°	8678.4
9°	7125.0
10°	5694.0
11°	4482.8
12°	3528.8
13°	2777.0
14°	2193.5
15°	1730.7
16°	1365.4
17°	1087.0
18°	874.2
19°	711.1
20°	587.0
22.5°	379.5
25°	250.0
26°	211.0
27°	179.1
28°	150.7
29°	125.9
30°	108.2
32.5°	74.5
35°	53.2
37.5°	39.0
40°	28.4
42.5°	19.5
45°	12.4
47.5°	8.9
50°	7.1
52.5°	5.3
55°	3.5
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.8



TEST NUMBER: P264013

CATALOG NUMBER: LD2B20D010 EU2B2010SP158030 2LBSQC*MB

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)