

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224585

Luminaire Tested: **LD2B20D010 EU2B20FL408030 2LBDL\*GPH**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224585  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B20FL408030 2LBDL\*GPH  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
LENSED SPUN ROUND TRIM WITH GRAPHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1763.7 lumens  
Efficiency: N/A  
Efficacy: 84.4 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224585

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDL\*GPH

### Luminous Intensity Polar Plot



0% Up  
100% Dn



TEST NUMBER: P224585

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDL\*GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	99	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	96	93	91	94	92	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83	83	83	83
5	98	91	86	83	96	90	85	82	88	84	81	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	85	81	78	83	80	77	82	79	77	75	75	75	75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72	72	72	72
8	87	80	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69	69	69	69
9	84	76	72	68	83	76	71	68	75	71	68	74	70	68	73	70	68	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1599971
5°	1567589
10°	1392948
15°	1092833
20°	735003
25°	427645
30°	214197
35°	99963
40°	46620
45°	19720
50°	9461
55°	6078
60°	3486
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224585

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDL\*GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	369.0	20.9
10°-20°	739.7	41.9
20°-30°	467.7	26.5
30°-40°	145.5	8.3
40°-50°	32.3	1.8
50°-60°	8.2	0.5
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1576.5	89.4
0°-40°	1722.0	97.6
0°-60°	1762.6	99.9
0°-90°	1763.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1763.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4131	
5°	4032	369
15°	2725	740
25°	1001	468
35°	211	146
45°	36	32
55°	9	8
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224585

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDL\*GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4130.6
2.5°	4112.6
5°	4031.6
7.5°	3840.5
10°	3541.5
12.5°	3163.7
15°	2725.2
17.5°	2250.8
20°	1783.1
22.5°	1362.6
25°	1000.6
27.5°	701.5
30°	478.9
32.5°	317.0
35°	211.4
37.5°	141.7
40°	92.2
42.5°	56.2
45°	36.0
47.5°	24.7
50°	15.7
52.5°	11.2
55°	9.0
57.5°	6.7
60°	4.5
62.5°	2.2
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)