

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224782

Luminaire Tested: **LD2B20D010 EU2B20FL408030 2LBDL**MW***

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224782
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL408030 2LBDL*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1739.4 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224782

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDL*MW

Luminous Intensity Polar Plot





TEST NUMBER: P224782

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1574716
5°	1546009
10°	1374304
15°	1080883
20°	719215
25°	412901
30°	208561
35°	98119
40°	39491
45°	19556
50°	10787
55°	7564
60°	6895
65°	4124
70°	5096
75°	3292
80°	4907
85°	0



TEST NUMBER: P224782

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	364.1	20.9
10°-20°	730.1	42.0
20°-30°	454.2	26.1
30°-40°	139.7	8.0
40°-50°	30.7	1.8
50°-60°	10.9	0.6
60°-70°	5.5	0.3
70°-80°	3.2	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1548.5	89.0
0°-40°	1688.1	97.1
0°-60°	1729.7	99.4
0°-90°	1739.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1739.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4065	
5°	3976	364
15°	2695	730
25°	966	454
35°	208	140
45°	36	31
55°	11	11
65°	4	6
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224782

CATALOG NUMBER: LD2B20D010 EU2B20FL408030 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4065.4
2.5°	4047.5
5°	3976.1
7.5°	3795.4
10°	3494.1
12.5°	3132.7
15°	2695.4
17.5°	2217.9
20°	1744.8
22.5°	1323.1
25°	966.1
27.5°	680.5
30°	466.3
32.5°	314.6
35°	207.5
37.5°	125.0
40°	78.1
42.5°	53.6
45°	35.7
47.5°	24.5
50°	17.9
52.5°	15.6
55°	11.2
57.5°	8.9
60°	8.9
62.5°	6.7
65°	4.5
67.5°	4.5
70°	4.5
72.5°	4.5
75°	2.2
77.5°	2.2
80°	2.2
82.5°	2.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)