

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224908

Luminaire Tested: **LD2B05D010 EU2B05FL409040 2LBD*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224908
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (156)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05FL409040 2LBD*H
Description: 500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 655.0 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224908

CATALOG NUMBER: LD2B05D010 EU2B05FL409040 2LBD*H

Luminous Intensity Polar Plot





TEST NUMBER: P224908

CATALOG NUMBER: LD2B05D010 EU2B05FL409040 2LBD*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 95 | | | 95 |
| 2 | 110 | 106 | 103 | 100 | 108 | 104 | 101 | 99 | 101 | 99 | 97 | 98 | 96 | 94 | 96 | 94 | 93 | 91 | | | 91 |
| 3 | 106 | 100 | 96 | 93 | 104 | 99 | 95 | 92 | 97 | 94 | 91 | 94 | 92 | 90 | 92 | 90 | 88 | 87 | | | 87 |
| 4 | 102 | 96 | 91 | 88 | 100 | 94 | 90 | 87 | 92 | 89 | 86 | 91 | 88 | 85 | 89 | 86 | 84 | 83 | | | 83 |
| 5 | 98 | 91 | 86 | 83 | 96 | 90 | 86 | 82 | 89 | 85 | 82 | 87 | 84 | 81 | 86 | 83 | 80 | 79 | | | 79 |
| 6 | 94 | 87 | 82 | 79 | 93 | 86 | 82 | 78 | 85 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 77 | 76 | | | 76 |
| 7 | 91 | 83 | 78 | 75 | 90 | 83 | 78 | 75 | 82 | 77 | 74 | 80 | 77 | 74 | 79 | 76 | 74 | 73 | | | 73 |
| 8 | 88 | 80 | 75 | 72 | 87 | 79 | 75 | 72 | 78 | 74 | 71 | 77 | 74 | 71 | 77 | 73 | 71 | 70 | | | 70 |
| 9 | 85 | 77 | 72 | 69 | 84 | 76 | 72 | 69 | 75 | 71 | 68 | 75 | 71 | 68 | 74 | 70 | 68 | 67 | | | 67 |
| 10 | 82 | 74 | 69 | 66 | 81 | 73 | 69 | 66 | 73 | 69 | 66 | 72 | 68 | 66 | 71 | 68 | 65 | 64 | | | 64 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 607552 |
| 5° | 594825 |
| 10° | 523865 |
| 15° | 410995 |
| 20° | 272921 |
| 25° | 156681 |
| 30° | 78585 |
| 35° | 36269 |
| 40° | 14765 |
| 45° | 6628 |
| 50° | 3435 |
| 55° | 2161 |
| 60° | 1007 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P224908

CATALOG NUMBER: LD2B05D010 EU2B05FL409040 2LBD*H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 139.7 | 21.3 |
| 10°-20° | 277.4 | 42.4 |
| 20°-30° | 172.4 | 26.3 |
| 30°-40° | 52.0 | 7.9 |
| 40°-50° | 10.6 | 1.6 |
| 50°-60° | 2.7 | 0.4 |
| 60°-70° | 0.2 | 0.0 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 589.5 | 90.0 |
| 0°-40° | 641.5 | 97.9 |
| 0°-60° | 654.9 | 100.0 |
| 0°-90° | 655.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 655.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1568 | |
| 5° | 1530 | 140 |
| 15° | 1025 | 277 |
| 25° | 367 | 172 |
| 35° | 77 | 52 |
| 45° | 12 | 11 |
| 55° | 3 | 3 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P224908

CATALOG NUMBER: LD2B05D010 EU2B05FL409040 2LBD*H

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1568.5 |
| 1° | 1563.4 |
| 2° | 1556.4 |
| 3° | 1551.3 |
| 4° | 1543.7 |
| 5° | 1529.8 |
| 6° | 1507.6 |
| 7° | 1477.1 |
| 8° | 1433.4 |
| 9° | 1383.9 |
| 10° | 1331.9 |
| 11° | 1276.7 |
| 12° | 1219.0 |
| 13° | 1158.7 |
| 14° | 1092.8 |
| 15° | 1024.9 |
| 17.5° | 842.9 |
| 20° | 662.1 |
| 22.5° | 502.3 |
| 25° | 366.6 |
| 27.5° | 258.8 |
| 30° | 175.7 |
| 32.5° | 115.4 |
| 35° | 76.7 |
| 37.5° | 47.6 |
| 40° | 29.2 |
| 42.5° | 19.0 |
| 45° | 12.1 |
| 47.5° | 7.6 |
| 50° | 5.7 |
| 52.5° | 3.8 |
| 55° | 3.2 |
| 57.5° | 1.9 |
| 60° | 1.3 |
| 62.5° | 0.0 |
| 65° | 0.0 |
| 67.5° | 0.0 |
| 70° | 0.0 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |



TEST NUMBER: P224908

CATALOG NUMBER: LD2B05D010 EU2B05FL409040 2LBD*H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 0.0 |
| 87.5° | | 0.0 |



(END OF REPORT)