

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224713

Luminaire Tested: **LD2B05D010 EU2B05FL409040 2LBD\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224713  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B05D010 EU2B05FL409040 2LBD\*MW  
Description: 500 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
SPUN ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 654.0 lumens  
Efficiency: N/A  
Efficacy: 89.6 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 7.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224713

CATALOG NUMBER: LD2B05D010 EU2B05FL409040 2LBD\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P224713

CATALOG NUMBER: LD2B05D010 EU2B05FL409040 2LBD\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86	86	86	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82	82	82	82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79	79	79	79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	592058
5°	581294
10°	516746
15°	406384
20°	270406
25°	155270
30°	78406
35°	36883
40°	14866
45°	7340
50°	4037
55°	2836
60°	2634
65°	1558
70°	1925
75°	1197
80°	1785
85°	0



TEST NUMBER: P224713

CATALOG NUMBER: LD2B05D010 EU2B05FL409040 2LBD\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.9	20.9
10°-20°	274.5	42.0
20°-30°	170.8	26.1
30°-40°	52.5	8.0
40°-50°	11.5	1.8
50°-60°	4.1	0.6
60°-70°	2.1	0.3
70°-80°	1.2	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.2	89.0
0°-40°	634.7	97.1
0°-60°	650.4	99.4
0°-90°	654.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	654.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1528	
5°	1495	137
15°	1013	275
25°	363	171
35°	78	53
45°	13	12
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P224713

CATALOG NUMBER: LD2B05D010 EU2B05FL409040 2LBD\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1528.5
2.5°	1521.8
5°	1495.0
7.5°	1427.0
10°	1313.8
12.5°	1177.9
15°	1013.4
17.5°	833.9
20°	656.0
22.5°	497.5
25°	363.3
27.5°	255.9
30°	175.3
32.5°	118.3
35°	78.0
37.5°	47.0
40°	29.4
42.5°	20.1
45°	13.4
47.5°	9.2
50°	6.7
52.5°	5.9
55°	4.2
57.5°	3.4
60°	3.4
62.5°	2.5
65°	1.7
67.5°	1.7
70°	1.7
72.5°	1.7
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)