

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B20D010 EU2B20WFL558030 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20WFL558030 2LBDLC*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1586.8 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: LD2B20D010 EU2B20WFL558030 2LBDLC**MW*

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL558030 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93			
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80			
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74			
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60			
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56			
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53			
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	744363
5°	739585
10°	687605
15°	603600
20°	520326
25°	444955
30°	353119
35°	246125
40°	155738
45°	95042
50°	56223
55°	30727
60°	6740
65°	5958
70°	4870
75°	6435
80°	4907
85°	9777



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL558030 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.5	11.1
10°-20°	419.2	26.4
20°-30°	473.0	29.8
30°-40°	327.2	20.6
40°-50°	139.5	8.8
50°-60°	40.3	2.5
60°-70°	5.9	0.4
70°-80°	3.7	0.2
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1068.7	67.4
0°-40°	1395.9	88.0
0°-60°	1575.7	99.3
0°-90°	1586.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1586.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1922	
5°	1902	177
15°	1505	419
25°	1041	473
35°	520	327
45°	174	139
55°	46	40
65°	6	6
75°	4	4
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL558030 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1921.7
2.5°	1919.5
5°	1902.1
7.5°	1843.6
10°	1748.2
12.5°	1631.0
15°	1505.2
17.5°	1375.1
20°	1262.3
22.5°	1156.0
25°	1041.1
27.5°	919.6
30°	789.5
32.5°	648.5
35°	520.5
37.5°	403.4
40°	308.0
42.5°	232.1
45°	173.5
47.5°	125.8
50°	93.3
52.5°	67.2
55°	45.5
57.5°	19.5
60°	8.7
62.5°	6.5
65°	6.5
67.5°	4.3
70°	4.3
72.5°	4.3
75°	4.3
77.5°	2.2
80°	2.2
82.5°	2.2
85°	2.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)