

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B20D010 EU2B20WFL559030 2LBD*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20WFL559030 2LBD*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
SPUN ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1427.0 lumens
Efficiency: N/A
Efficacy: 68.3 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559030 2LBD*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559030 2LBD*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93			
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80			
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74			
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64			
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60			
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56			
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53			
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	669334
5°	665086
10°	618301
15°	542807
20°	467894
25°	400122
30°	317516
35°	221347
40°	140063
45°	85455
50°	50558
55°	27688
60°	6043
65°	5408
70°	4417
75°	5837
80°	4461
85°	8889



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559030 2LBD*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	11.1
10°-20°	377.0	26.4
20°-30°	425.3	29.8
30°-40°	294.2	20.6
40°-50°	125.4	8.8
50°-60°	36.3	2.5
60°-70°	5.3	0.4
70°-80°	3.4	0.2
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	961.0	67.3
0°-40°	1255.3	88.0
0°-60°	1417.0	99.3
0°-90°	1427.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1427.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1728	
5°	1710	159
15°	1354	377
25°	936	425
35°	468	294
45°	156	125
55°	41	36
65°	6	5
75°	4	3
85°	2	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559030 2LBD*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1728.0
2.5°	1726.1
5°	1710.5
7.5°	1657.8
10°	1572.0
12.5°	1466.7
15°	1353.6
17.5°	1236.5
20°	1135.1
22.5°	1039.5
25°	936.2
27.5°	827.0
30°	709.9
32.5°	583.2
35°	468.1
37.5°	362.8
40°	277.0
42.5°	208.7
45°	156.0
47.5°	113.1
50°	83.9
52.5°	60.5
55°	41.0
57.5°	17.6
60°	7.8
62.5°	5.9
65°	5.9
67.5°	3.9
70°	3.9
72.5°	3.9
75°	3.9
77.5°	2.0
80°	2.0
82.5°	2.0
85°	2.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)