

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B20D010 EU2B20WFL559030 2LBDL*H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14807)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20WFL559030 2LBDL*H
Description: 2000 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1310.6 lumens
Efficiency: N/A
Efficacy: 62.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559030 2LBDL*H

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559030 2LBDL*H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93			
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80			
4	96	89	83	79	95	87	82	78	85	81	77	83	79	76	81	78	75	74			
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	68			
6	87	77	71	67	85	77	71	67	75	70	66	74	69	66	72	68	65	64			
7	82	73	66	62	81	72	66	62	71	65	62	69	65	61	68	64	61	59			
8	78	68	62	58	77	68	62	58	67	61	57	66	61	57	65	60	57	56			
9	74	64	58	54	73	64	58	54	63	58	54	62	57	54	61	57	54	52			
10	71	61	55	51	70	60	55	51	60	54	51	59	54	51	58	54	50	49			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	614834
5°	602913
10°	560444
15°	496210
20°	429559
25°	361101
30°	282763
35°	202054
40°	134906
45°	83648
50°	50076
55°	30052
60°	13480
65°	1741
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559030 2LBDL*H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.9	11.0
10°-20°	344.6	26.3
20°-30°	384.4	29.3
30°-40°	269.2	20.5
40°-50°	122.9	9.4
50°-60°	41.1	3.1
60°-70°	4.5	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	872.9	66.6
0°-40°	1142.1	87.1
0°-60°	1306.1	99.7
0°-90°	1310.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1310.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1587	
5°	1551	144
15°	1237	345
25°	845	384
35°	427	269
45°	153	123
55°	44	41
65°	2	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B20D010 EU2B20WFL559030 2LBDL*H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1587.3
2.5°	1579.6
5°	1550.6
7.5°	1496.4
10°	1424.9
12.5°	1334.0
15°	1237.4
17.5°	1136.8
20°	1042.1
22.5°	947.4
25°	844.9
27.5°	740.5
30°	632.2
32.5°	525.9
35°	427.3
37.5°	340.3
40°	266.8
42.5°	203.0
45°	152.7
47.5°	114.1
50°	83.1
52.5°	59.9
55°	44.5
57.5°	30.9
60°	17.4
62.5°	5.8
65°	1.9
67.5°	1.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)