

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P223985

Luminaire Tested: **LD2B05D010 EU2B05SP158050 2LBDSQLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P223985
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (150)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05SP158050 2LBDSQLC*MW
Description: 500 Lumen, 2inch Portfolio LED Downlight
SPOT OPTIC
LENSED SQUARE CAST TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 438.0 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 0.24 / 0.24 / 0.23
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P223985

CATALOG NUMBER: LD2B05D010 EU2B05SP158050 2LBDSQLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P223985

CATALOG NUMBER: LD2B05D010 EU2B05SP158050 2LBDSQLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																																				
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96																																				
3	110	106	103	101	108	105	102	100	102	100	98	100	98	97	98	97	96	94																																				
4	108	103	100	97	106	102	99	97	100	98	96	98	96	95	97	95	94	93																																				
5	105	101	97	95	104	100	97	94	98	96	94	97	95	93	95	94	92	91																																				
6	103	98	95	93	102	98	95	92	96	94	92	95	93	91	94	92	91	90																																				
7	101	96	93	91	100	96	93	90	95	92	90	94	91	90	93	91	89	88																																				
8	100	94	91	89	99	94	91	89	93	90	89	92	90	88	92	90	88	87																																				
9	98	93	90	88	97	92	89	87	92	89	87	91	89	87	90	88	87	86																																				
10	96	91	88	86	96	91	88	86	90	88	86	90	87	86	89	87	86	85																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2104683
5°	1521475
10°	442959
15°	155432
20°	66530
25°	29960
30°	11584
35°	5769
40°	3843
45°	2520
50°	1386
55°	1013
60°	620
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P223985

CATALOG NUMBER: LD2B05D010 EU2B05SP158050 2LBDSQLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.9	63.2
10°-20°	112.6	25.7
20°-30°	34.6	7.9
30°-40°	8.5	1.9
40°-50°	3.6	0.8
50°-60°	1.5	0.3
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	424.1	96.8
0°-40°	432.7	98.8
0°-60°	437.7	99.9
0°-90°	438.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	438.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5434	
5°	3913	277
15°	388	113
25°	70	35
35°	12	9
45°	5	4
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P223985

CATALOG NUMBER: LD2B05D010 EU2B05SP158050 2LBDSQLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5433.6
1°	5350.6
2°	5148.1
3°	4825.2
4°	4403.4
5°	3913.0
6°	3360.2
7°	2760.2
8°	2151.8
9°	1583.0
10°	1126.2
11°	807.1
12°	606.9
13°	494.2
14°	432.5
15°	387.6
17.5°	239.1
20°	161.4
22.5°	108.1
25°	70.1
27.5°	42.6
30°	25.9
32.5°	16.8
35°	12.2
37.5°	9.9
40°	7.6
42.5°	6.1
45°	4.6
47.5°	3.0
50°	2.3
52.5°	2.3
55°	1.5
57.5°	1.5
60°	0.8
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P223985

CATALOG NUMBER: LD2B05D010 EU2B05SP158050 2LBDSQLC*MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)