

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225431

Luminaire Tested: **LD2B20D010 EU2B20FL409730 2LBDLC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225431
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14833)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL409730 2LBDLC*MB
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1259.8 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225431

CATALOG NUMBER: LD2B20D010 EU2B20FL409730 2LBDLC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225431

CATALOG NUMBER: LD2B20D010 EU2B20FL409730 2LBDLC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	95	92	103	98	94	91	96	92	90	93	91	88	91	89	87	86	86	86	86
4	101	94	90	86	99	93	89	86	91	87	85	89	86	84	88	85	83	81	81	81	81
5	97	90	85	81	95	89	84	81	87	83	80	85	82	79	84	81	79	77	77	77	77
6	93	85	80	77	92	85	80	76	83	79	76	82	78	75	81	77	75	74	74	74	74
7	89	81	76	73	88	81	76	73	80	75	72	79	75	72	78	74	72	70	70	70	70
8	86	78	73	69	85	77	73	69	76	72	69	75	72	69	75	71	68	67	67	67	67
9	83	75	70	66	82	74	69	66	73	69	66	72	69	66	72	68	65	64	64	64	64
10	80	72	67	63	79	71	66	63	70	66	63	70	66	63	69	65	63	62	62	62	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1095492
5°	1056206
10°	928947
15°	728114
20°	504333
25°	310712
30°	172869
35°	92208
40°	45710
45°	23336
50°	12835
55°	8374
60°	4106
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225431

CATALOG NUMBER: LD2B20D010 EU2B20FL409730 2LBDLC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.8	19.7
10°-20°	495.9	39.4
20°-30°	338.8	26.9
30°-40°	129.1	10.3
40°-50°	35.9	2.8
50°-60°	11.2	0.9
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1082.5	85.9
0°-40°	1211.6	96.2
0°-60°	1258.7	99.9
0°-90°	1259.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1259.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2828	
5°	2716	248
15°	1816	496
25°	727	339
35°	195	129
45°	43	36
55°	12	11
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225431

CATALOG NUMBER: LD2B20D010 EU2B20FL409730 2LBDLC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2828.2
2.5°	2798.0
5°	2716.4
7.5°	2564.0
10°	2361.8
12.5°	2104.7
15°	1815.7
17.5°	1519.6
20°	1223.5
22.5°	961.0
25°	727.0
27.5°	533.7
30°	386.5
32.5°	274.8
35°	195.0
37.5°	136.5
40°	90.4
42.5°	60.3
45°	42.6
47.5°	30.1
50°	21.3
52.5°	16.0
55°	12.4
57.5°	8.9
60°	5.3
62.5°	1.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)