

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224362

Luminaire Tested: **LD2B20D010 EU2B20FL409730 2LBDSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL409730 2LBDSQC*MMS
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1309.1 lumens
Efficiency: N/A
Efficacy: 62.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224362

CATALOG NUMBER: LD2B20D010 EU2B20FL409730 2LBDSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224362

CATALOG NUMBER: LD2B20D010 EU2B20FL409730 2LBDSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																																				
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91																																				
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87																																				
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83																																				
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	82	80	79																																				
6	94	87	82	78	93	86	82	78	85	81	78	83	80	77	82	79	77	76																																				
7	91	83	78	75	89	82	78	75	81	77	74	80	77	74	79	76	73	72																																				
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69																																				
9	84	76	72	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67																																				
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1191631
5°	1168771
10°	1038211
15°	819304
20°	546460
25°	314516
30°	159317
35°	74665
40°	30591
45°	13804
50°	7111
55°	4525
60°	2634
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224362

CATALOG NUMBER: LD2B20D010 EU2B20FL409730 2LBDSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	275.1	21.0
10°-20°	552.1	42.2
20°-30°	345.8	26.4
30°-40°	107.0	8.2
40°-50°	22.1	1.7
50°-60°	6.1	0.5
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1173.0	89.6
0°-40°	1280.0	97.8
0°-60°	1308.3	99.9
0°-90°	1309.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1309.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3076	
5°	3006	275
15°	2043	552
25°	736	346
35°	158	107
45°	25	22
55°	7	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224362

CATALOG NUMBER: LD2B20D010 EU2B20FL409730 2LBDSQC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	3076.4
2.5°	3061.3
5°	3005.9
7.5°	2864.7
10°	2639.6
12.5°	2362.4
15°	2043.1
17.5°	1675.2
20°	1325.7
22.5°	1008.1
25°	735.9
27.5°	517.5
30°	356.2
32.5°	238.6
35°	157.9
37.5°	99.1
40°	60.5
42.5°	38.6
45°	25.2
47.5°	16.8
50°	11.8
52.5°	8.4
55°	6.7
57.5°	5.0
60°	3.4
62.5°	1.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)