

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224337

Luminaire Tested: **LD2B05D010 EU2B05FL409050 2LBDSQC*MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05FL409050 2LBDSQC*MMS
Description: 500 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
SQUARE CAST TRIM WITH MATTE METALLIC SILVER
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 641.7 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224337

CATALOG NUMBER: LD2B05D010 EU2B05FL409050 2LBDSQC*MMS

Luminous Intensity Polar Plot





TEST NUMBER: P224337

CATALOG NUMBER: LD2B05D010 EU2B05FL409050 2LBDSQC*MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	110	106	102	100	108	104	101	99	101	99	96	98	96	94	95	94	92	91			91																
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87			87																
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83			83																
5	98	91	86	83	96	90	86	82	88	85	82	87	83	81	85	83	80	79			79																
6	94	87	82	78	93	86	82	78	85	81	78	83	80	77	82	79	77	76			76																
7	91	83	78	75	89	82	78	75	81	77	74	80	77	74	79	76	73	72			72																
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69			69																
9	84	76	72	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67			67																
10	81	74	69	66	81	73	69	66	72	68	65	72	68	65	71	68	65	64			64																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	584118
5°	572896
10°	508919
15°	401612
20°	267851
25°	154159
30°	78093
35°	36600
40°	14967
45°	6793
50°	3495
55°	2229
60°	1240
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224337

CATALOG NUMBER: LD2B05D010 EU2B05FL409050 2LBDSQC*MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.9	21.0
10°-20°	270.6	42.2
20°-30°	169.5	26.4
30°-40°	52.4	8.2
40°-50°	10.8	1.7
50°-60°	3.0	0.5
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	575.0	89.6
0°-40°	627.4	97.8
0°-60°	641.3	99.9
0°-90°	641.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	641.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1508	
5°	1473	135
15°	1002	271
25°	361	170
35°	77	52
45°	12	11
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224337

CATALOG NUMBER: LD2B05D010 EU2B05FL409050 2LBDSQC*MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1508.0
2.5°	1500.6
5°	1473.4
7.5°	1404.2
10°	1293.9
12.5°	1158.0
15°	1001.5
17.5°	821.1
20°	649.8
22.5°	494.2
25°	360.7
27.5°	253.7
30°	174.6
32.5°	116.9
35°	77.4
37.5°	48.6
40°	29.6
42.5°	18.9
45°	12.4
47.5°	8.2
50°	5.8
52.5°	4.1
55°	3.3
57.5°	2.5
60°	1.6
62.5°	0.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)