

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264111

Luminaire Tested: **LD2B20D010 EU2B2010SP158040 2LBD*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264111
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP158040 2LBD*WH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1841.0 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264111

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBD*WH

Luminous Intensity Polar Plot





TEST NUMBER: P264111

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBD*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98			98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96			96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94			94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92			92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90			90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89			89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87			87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86			86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85			85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83			83

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8686966
5°	6963015
10°	3039051
15°	941801
20°	328298
25°	145019
30°	65628
35°	34149
40°	19450
45°	9210
50°	5833
55°	3269
60°	1875
65°	2218
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264111

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBD*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1067.7	58.0
10°-20°	584.7	31.8
20°-30°	133.3	7.2
30°-40°	38.3	2.1
40°-50°	11.8	0.6
50°-60°	3.6	0.2
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1785.7	97.0
0°-40°	1824.0	99.1
0°-60°	1839.4	99.9
0°-90°	1841.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1841.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17608	
5°	14060	###
15°	1844	585
25°	266	133
35°	57	38
45°	13	12
55°	4	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264111

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBD*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	17607.7
1°	17388.5
2°	16933.2
3°	16226.7
4°	15255.6
5°	14059.7
6°	12593.7
7°	10955.7
8°	9245.9
9°	7591.0
10°	6066.3
11°	4776.0
12°	3759.6
13°	2958.5
14°	2337.0
15°	1843.9
16°	1454.7
17°	1158.1
18°	931.4
19°	757.6
20°	625.3
22.5°	404.3
25°	266.4
26°	224.8
27°	190.8
28°	160.6
29°	134.1
30°	115.2
32.5°	79.3
35°	56.7
37.5°	41.6
40°	30.2
42.5°	20.8
45°	13.2
47.5°	9.4
50°	7.6
52.5°	5.7
55°	3.8
57.5°	1.9
60°	1.9
62.5°	1.9
65°	1.9
67.5°	1.9



TEST NUMBER: P264111

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBD*WH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)