

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264785

Luminaire Tested: **LD2B20D010 EU2B2010SP158040 2LBDL*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P264785
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP158040 2LBDL*MW
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1841.0 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P264785

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBDL**MW*

Luminous Intensity Polar Plot





TEST NUMBER: P264785

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBDL*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97											97																	
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94											94																	
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92											92																	
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89											89																	
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87											87																	
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85											85																	
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83											83																	
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81											81																	
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79											79																	
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78											78																	

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6499104
5°	5289627
10°	2857348
15°	1139263
20°	456824
25°	218780
30°	113424
35°	59927
40°	33232
45°	20583
50°	14123
55°	9548
60°	7302
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264785

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBDL*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	859.0	46.7
10°-20°	677.7	36.8
20°-30°	199.9	10.9
30°-40°	66.6	3.6
40°-50°	25.0	1.4
50°-60°	11.1	0.6
60°-70°	1.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1736.6	94.3
0°-40°	1803.1	97.9
0°-60°	1839.2	99.9
0°-90°	1841.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1841.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13173	
5°	10681	859
15°	2230	678
25°	402	200
35°	100	67
45°	30	25
55°	11	11
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264785

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBDL*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	13173.1
2.5°	12642.2
5°	10680.8
7.5°	8229.0
10°	5703.6
12.5°	3650.0
15°	2230.5
17.5°	1360.4
20°	870.1
22.5°	582.5
25°	401.9
27.5°	283.9
30°	199.1
32.5°	140.1
35°	99.5
37.5°	70.1
40°	51.6
42.5°	40.6
45°	29.5
47.5°	25.8
50°	18.4
52.5°	14.7
55°	11.1
57.5°	11.1
60°	7.4
62.5°	3.7
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)