

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P#

Luminaire Tested: **LD2B05D010 EU2B05WFL559050 2LBDLC*MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14810)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B05D010 EU2B05WFL559050 2LBDLC*MW
Description: 500 Lumen, 2inch Portfolio LED Downlight
WIDE FLOOD OPTIC
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 576.1 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.84
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05WFL559050 2LBDLC*MW

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05WFL559050 2LBDLC*MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93
2	108	102	98	95	105	101	97	94	98	94	92	95	92	90	92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80
4	97	89	83	79	95	88	82	78	85	81	77	83	80	76	82	78	76	74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69
6	87	78	71	67	85	77	71	67	75	70	66	74	69	66	73	69	65	64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60
8	78	69	62	58	77	68	62	58	67	62	58	66	61	58	65	61	57	56
9	74	65	59	55	73	64	58	54	63	58	54	62	57	54	61	57	54	53
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	270213
5°	268484
10°	249602
15°	219112
20°	188872
25°	161510
30°	128187
35°	89371
40°	56531
45°	34511
50°	20428
55°	11143
60°	2402
65°	2200
70°	1812
75°	2395
80°	1785
85°	3555



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05WFL559050 2LBDLC*MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.1	11.1
10°-20°	152.2	26.4
20°-30°	171.7	29.8
30°-40°	118.8	20.6
40°-50°	50.6	8.8
50°-60°	14.6	2.5
60°-70°	2.2	0.4
70°-80°	1.4	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	387.9	67.3
0°-40°	506.7	88.0
0°-60°	572.0	99.3
0°-90°	576.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	576.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	698	
5°	690	64
15°	546	152
25°	378	172
35°	189	119
45°	63	51
55°	16	15
65°	2	2
75°	2	1
85°	1	1
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: LD2B05D010 EU2B05WFL559050 2LBDLC*MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	697.6
2.5°	696.8
5°	690.5
7.5°	669.2
10°	634.6
12.5°	592.1
15°	546.4
17.5°	499.2
20°	458.2
22.5°	419.6
25°	377.9
27.5°	333.8
30°	286.6
32.5°	235.4
35°	189.0
37.5°	146.4
40°	111.8
42.5°	84.2
45°	63.0
47.5°	45.7
50°	33.9
52.5°	24.4
55°	16.5
57.5°	7.1
60°	3.1
62.5°	2.4
65°	2.4
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)