

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279435

Luminaire Tested: **LDA2B108027D010 EU2B10FL408027 2LBALD1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279435  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B108027D010 EU2B10FL408027 2LBALD1H  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl w/lens Self-Flanged, LI  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1144.4 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279435

CATALOG NUMBER: LDA2B108027D010 EU2B10FL408027 2LBALD1H

### Luminous Intensity Polar Plot





TEST NUMBER: P279435

CATALOG NUMBER: LDA2B108027D010 EU2B10FL408027 2LBALD1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96																												
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92																												
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89																												
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85																												
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82																												
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79																												
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77																												
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74																												
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72																												
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1573577
5°	1540266
10°	1403876
15°	1096716
20°	649298
25°	241371
30°	75426
35°	33547
40°	15586
45°	7326
50°	4068
55°	2236
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P279435

CATALOG NUMBER: LDA2B108027D010 EU2B10FL408027 2LBALD1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	287.5	25.1
10°-20°	571.7	50.0
20°-30°	234.1	20.5
30°-40°	38.8	3.4
40°-50°	9.2	0.8
50°-60°	2.5	0.2
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1093.4	95.5
0°-40°	1132.1	98.9
0°-60°	1143.8	99.9
0°-90°	1144.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1144.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3190	
5°	3110	287
15°	2147	572
25°	443	234
35°	56	39
45°	10	9
55°	3	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279435

CATALOG NUMBER: LDA2B108027D010 EU2B10FL408027 2LBALD1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3189.5
1°	3178.4
2°	3163.7
3°	3150.6
4°	3133.3
5°	3110.1
6°	3076.0
7°	3031.3
8°	2967.8
9°	2890.5
10°	2802.3
11°	2699.8
12°	2584.3
13°	2452.4
14°	2305.8
15°	2147.2
17.5°	1702.7
20°	1236.7
22.5°	791.7
25°	443.4
27.5°	233.8
30°	132.4
32.5°	84.1
35°	55.7
37.5°	36.8
40°	24.2
42.5°	15.8
45°	10.5
47.5°	7.4
50°	5.3
52.5°	3.7
55°	2.6
57.5°	1.6
60°	1.1
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279435

CATALOG NUMBER: LDA2B108027D010 EU2B10FL408027 2LBALD1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)