

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264119

Luminaire Tested: **LD2B20D010 EU2B2010SP158040 2LBSQC\*MMS**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264119  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B2010SP158040 2LBSQC\*MMS  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1919.0 lumens  
Efficiency: N/A  
Efficacy: 91.8 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264119

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBSQC\*MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P264119

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBSQC\*MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98			98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96			96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94			94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92			92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90			90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89			89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87			87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86			86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85			85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83			83

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	9055014
5°	7258033
10°	3167851
15°	981692
20°	342211
25°	151170
30°	68419
35°	35595
40°	20287
45°	9629
50°	6064
55°	3355
60°	1973
65°	2335
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264119

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBSQC\*MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1112.9	58.0
10°-20°	609.5	31.8
20°-30°	138.9	7.2
30°-40°	39.9	2.1
40°-50°	12.3	0.6
50°-60°	3.7	0.2
60°-70°	1.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1861.3	97.0
0°-40°	1901.3	99.1
0°-60°	1917.3	99.9
0°-90°	1919.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1919.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	18354	
5°	14655	###
15°	1922	609
25°	278	139
35°	59	40
45°	14	12
55°	4	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264119

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBSQC\*MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	18353.7
1°	18125.3
2°	17650.7
3°	16914.2
4°	15901.9
5°	14655.4
6°	13127.2
7°	11419.9
8°	9637.7
9°	7912.6
10°	6323.4
11°	4978.3
12°	3918.9
13°	3083.9
14°	2436.0
15°	1922.0
16°	1516.3
17°	1207.2
18°	970.9
19°	789.7
20°	651.8
22.5°	421.4
25°	277.7
26°	234.3
27°	198.9
28°	167.4
29°	139.8
30°	120.1
32.5°	82.7
35°	59.1
37.5°	43.3
40°	31.5
42.5°	21.7
45°	13.8
47.5°	9.8
50°	7.9
52.5°	5.9
55°	3.9
57.5°	2.0
60°	2.0
62.5°	2.0
65°	2.0
67.5°	2.0



TEST NUMBER: P264119

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBSQC\*MMS

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)