

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P264118

Luminaire Tested: **LD2B20D010 EU2B2010SP158040 2LBSQC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P264118  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1805-787-1)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B2010SP158040 2LBSQC\*MW  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1668.0 lumens  
Efficiency: N/A  
Efficacy: 79.8 lumens/watt  
Spacing Criteria (0/90/45): 0.28 / 0.28 / 0.28  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P264118

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBSQC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P264118

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBSQC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	102	101	100	100	98			98
2	113	109	107	105	111	108	106	104	105	103	101	102	101	99	99	98	97	96			96
3	110	106	103	100	108	105	102	100	102	100	98	100	98	97	98	96	95	94			94
4	107	103	99	97	106	102	99	96	100	97	95	98	96	94	96	95	93	92			92
5	105	100	97	94	104	99	96	94	98	95	93	96	94	92	95	93	91	90			90
6	103	98	94	92	102	97	94	91	96	93	91	95	92	90	93	91	90	89			89
7	101	95	92	90	100	95	92	89	94	91	89	93	90	89	92	90	88	87			87
8	99	93	90	88	98	93	90	88	92	89	87	91	89	87	91	88	87	86			86
9	97	92	88	86	96	91	88	86	91	88	86	90	87	86	89	87	85	85			85
10	95	90	87	85	95	90	87	85	89	86	85	89	86	84	88	86	84	83			83

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	7870650
5°	6308696
10°	2753496
15°	853285
20°	297479
25°	131410
30°	59475
35°	30957
40°	17647
45°	8373
50°	5219
55°	2925
60°	1677
65°	1985
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P264118

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBSQC\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	967.3	58.0
10°-20°	529.8	31.8
20°-30°	120.8	7.2
30°-40°	34.7	2.1
40°-50°	10.7	0.6
50°-60°	3.2	0.2
60°-70°	1.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1617.9	97.0
0°-40°	1652.6	99.1
0°-60°	1666.5	99.9
0°-90°	1668.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1668.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	15953	
5°	12738	967
15°	1671	530
25°	241	121
35°	51	35
45°	12	11
55°	3	3
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P264118

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBSQC\*MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	15953.1
1°	15754.5
2°	15342.0
3°	14701.8
4°	13822.0
5°	12738.5
6°	11410.2
7°	9926.2
8°	8377.1
9°	6877.6
10°	5496.3
11°	4327.2
12°	3406.3
13°	2680.5
14°	2117.4
15°	1670.6
16°	1318.0
17°	1049.3
18°	843.9
19°	686.4
20°	566.6
22.5°	366.3
25°	241.4
26°	203.7
27°	172.9
28°	145.5
29°	121.5
30°	104.4
32.5°	71.9
35°	51.4
37.5°	37.7
40°	27.4
42.5°	18.8
45°	12.0
47.5°	8.6
50°	6.8
52.5°	5.1
55°	3.4
57.5°	1.7
60°	1.7
62.5°	1.7
65°	1.7
67.5°	1.7



TEST NUMBER: P264118

CATALOG NUMBER: LD2B20D010 EU2B2010SP158040 2LBSQC\*MW

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







70°		0.0
72.5°		0.0



(END OF REPORT)