

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494522

Luminaire Tested: **LDA2B108027R60D010 2LBD1MW**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494522  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-53)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/8/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108027R60D010 2LBD1MW  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1022.9 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.87  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494522  
CATALOG NUMBER: LDA2B108027R60D010 2LBD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P494522

CATALOG NUMBER: LDA2B108027R60D010 2LBD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82
4	98	91	86	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56
10	73	64	58	55	72	64	58	54	63	58	54	62	57	54	61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	612410
5°	581370
10°	569155
15°	550912
20°	503709
25°	447195
30°	334519
35°	188876
40°	71102
45°	31816
50°	15504
55°	3097
60°	987
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P494522

CATALOG NUMBER: LDA2B108027R60D010 2LBD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.1	10.9
10°-20°	299.6	29.3
20°-30°	366.0	35.8
30°-40°	199.6	19.5
40°-50°	39.9	3.9
50°-60°	5.7	0.6
60°-70°	0.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	776.7	75.9
0°-40°	976.3	95.5
0°-60°	1022.0	99.9
0°-90°	1022.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1022.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1241	
5°	1174	111
15°	1079	300
25°	822	366
35°	314	200
45°	46	40
55°	4	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494522

CATALOG NUMBER: LDA2B108027R60D010 2LBD1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1241.3
1°	1235.6
2°	1224.7
3°	1210.2
4°	1189.5
5°	1173.9
6°	1165.6
7°	1155.8
8°	1148.0
9°	1144.4
10°	1136.1
11°	1126.8
12°	1118.5
13°	1108.6
14°	1094.1
15°	1078.6
16°	1058.9
17°	1031.4
18°	1013.8
19°	985.3
20°	959.4
21°	935.5
22.5°	895.6
23°	879.0
24°	853.6
25°	821.5
26°	780.5
27°	737.5
28°	688.3
29°	641.6
30°	587.2
32.5°	450.4
35°	313.6
37.5°	196.4
40°	110.4
42.5°	68.9
45°	45.6
47.5°	31.1
50°	20.2
52.5°	10.4
55°	3.6
57.5°	1.6
60°	1.0
62.5°	1.0
65°	0.5



TEST NUMBER: P494522

CATALOG NUMBER: LDA2B108027R60D010 2LBD1MW

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)