

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494527

Luminaire Tested: **LDA2B108027R60D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494527  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-55)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108027R60D010 2LBDL1GPH  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 2700K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 943.5 lumens  
Efficiency: N/A  
Efficacy: 94.4 lumens/watt  
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.86  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494527  
CATALOG NUMBER: LDA2B108027R60D010 2LBDL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P494527

CATALOG NUMBER: LDA2B108027R60D010 2LBDL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	76	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	54	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	558436
5°	543929
10°	528927
15°	502696
20°	459344
25°	394447
30°	293502
35°	172313
40°	82115
45°	38305
50°	19112
55°	6709
60°	1579
65°	1167
70°	721
75°	953
80°	0
85°	0



TEST NUMBER: P494527

CATALOG NUMBER: LDA2B108027R60D010 2LBDL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.3	11.0
10°-20°	273.9	29.0
20°-30°	325.2	34.5
30°-40°	183.5	19.5
40°-50°	47.7	5.1
50°-60°	8.7	0.9
60°-70°	0.9	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	702.4	74.4
0°-40°	885.9	93.9
0°-60°	942.3	99.9
0°-90°	943.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	943.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1132	
5°	1098	103
15°	984	274
25°	725	325
35°	286	184
45°	55	48
55°	8	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494527

CATALOG NUMBER: LDA2B108027R60D010 2LBDL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1131.9
1°	1132.5
2°	1124.7
3°	1118.0
4°	1105.0
5°	1098.3
6°	1086.3
7°	1077.5
8°	1069.2
9°	1063.5
10°	1055.8
11°	1040.7
12°	1026.7
13°	1019.0
14°	1000.8
15°	984.2
16°	965.1
17°	942.3
18°	920.5
19°	894.6
20°	874.9
21°	847.9
22.5°	803.4
23°	795.6
24°	757.7
25°	724.6
26°	687.8
27°	645.3
28°	603.3
29°	562.3
30°	515.2
32.5°	396.5
35°	286.1
37.5°	195.4
40°	127.5
42.5°	83.4
45°	54.9
47.5°	37.3
50°	24.9
52.5°	15.5
55°	7.8
57.5°	3.1
60°	1.6
62.5°	1.0
65°	1.0



TEST NUMBER: P494527

CATALOG NUMBER: LDA2B108027R60D010 2LBDL1GPH

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)