

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P314957

Luminaire Tested: **LDA2B10NFL8027D010 PIN1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P314957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B10NFL8027D010 PIN1MMS
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, Black oculus, matte metallic silver finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 963.0 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314957

CATALOG NUMBER: LDA2B10NFL8027D010 PIN1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P314957

CATALOG NUMBER: LDA2B10NFL8027D010 PIN1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																			
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97									97																			
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94									94																			
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91									91																			
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89									89																			
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86									86																			
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84									84																			
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82									82																			
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80									80																			
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78									78																			
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76									76																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2464885
5°	2273230
10°	1531874
15°	755269
20°	322628
25°	126837
30°	49961
35°	21863
40°	10498
45°	5093
50°	2763
55°	1548
60°	888
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P314957

CATALOG NUMBER: LDA2B10NFL8027D010 PIN1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	388.8	40.4
10°-20°	418.7	43.5
20°-30°	120.9	12.6
30°-40°	25.5	2.6
40°-50°	6.3	0.7
50°-60°	1.8	0.2
60°-70°	0.6	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	928.5	96.4
0°-40°	954.0	99.1
0°-60°	962.1	99.9
0°-90°	963.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	963.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4996	
5°	4590	389
15°	1479	419
25°	233	121
35°	36	26
45°	7	6
55°	2	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P314957

CATALOG NUMBER: LDA2B10NFL8027D010 PIN1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	4996.1
1°	4964.7
2°	4911.6
3°	4839.8
4°	4738.1
5°	4590.1
6°	4390.2
7°	4129.5
8°	3808.9
9°	3435.2
10°	3057.8
11°	2676.3
12°	2316.1
13°	1996.4
14°	1715.3
15°	1478.7
17.5°	977.3
20°	614.5
22.5°	377.8
25°	233.0
27.5°	142.1
30°	87.7
32.5°	55.4
35°	36.3
37.5°	24.1
40°	16.3
42.5°	11.4
45°	7.3
47.5°	4.5
50°	3.6
52.5°	2.7
55°	1.8
57.5°	1.4
60°	0.9
62.5°	0.9
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.5
80°	0.0
82.5°	0.0



TEST NUMBER: P314957

CATALOG NUMBER: LDA2B10NFL8027D010 PIN1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)