

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279453

Luminaire Tested: **LDA2B108030D010 EU2B10FL408030 2LBALD1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P279453
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108030D010 EU2B10FL408030 2LBALD1B
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in
ADJ spun Refl w/lens Self-Flanged, B
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1156.3 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P279453

CATALOG NUMBER: LDA2B108030D010 EU2B10FL408030 2LBALD1B

Luminous Intensity Polar Plot





TEST NUMBER: P279453

CATALOG NUMBER: LDA2B108030D010 EU2B10FL408030 2LBALD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92		
3	107	102	98	95	105	101	97	94	98	95	93	96	94	92	94	92	90	89		
4	103	98	93	90	102	97	93	90	95	91	89	93	90	88	91	89	87	85		
5	100	94	89	86	98	93	89	86	91	88	85	90	87	84	88	86	83	82		
6	97	90	85	82	95	89	85	82	88	84	82	87	83	81	85	83	80	79		
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77		
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74		
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	73	72		
10	85	78	74	71	84	78	74	71	77	73	71	76	73	70	76	72	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1590056
5°	1556411
10°	1418554
15°	1108157
20°	656071
25°	243875
30°	76224
35°	33909
40°	15715
45°	7396
50°	4068
55°	2322
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P279453

CATALOG NUMBER: LDA2B108030D010 EU2B10FL408030 2LBALD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.5	25.1
10°-20°	577.7	50.0
20°-30°	236.6	20.5
30°-40°	39.2	3.4
40°-50°	9.2	0.8
50°-60°	2.5	0.2
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1104.8	95.5
0°-40°	1144.0	98.9
0°-60°	1155.7	99.9
0°-90°	1156.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1156.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3223	
5°	3143	291
15°	2170	578
25°	448	237
35°	56	39
45°	11	9
55°	3	2
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P279453

CATALOG NUMBER: LDA2B108030D010 EU2B10FL408030 2LBALD1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	3222.9
1°	3211.7
2°	3196.9
3°	3183.6
4°	3166.1
5°	3142.7
6°	3108.2
7°	3063.1
8°	2998.8
9°	2920.8
10°	2831.6
11°	2728.1
12°	2611.3
13°	2478.1
14°	2330.0
15°	2169.6
17.5°	1720.5
20°	1249.6
22.5°	800.0
25°	448.0
27.5°	236.2
30°	133.8
32.5°	84.9
35°	56.3
37.5°	37.2
40°	24.4
42.5°	15.9
45°	10.6
47.5°	7.4
50°	5.3
52.5°	3.7
55°	2.7
57.5°	1.6
60°	1.1
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P279453

CATALOG NUMBER: LDA2B108030D010 EU2B10FL408030 2LBALD1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)