

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P265100

Luminaire Tested: **LD2B20D010 EU2B2010SP159040 2LBDL*WMH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P265100
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1711-432-2)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B2010SP159040 2LBDL*WMH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1417.0 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P265100

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBDL*WMH

Luminous Intensity Polar Plot





TEST NUMBER: P265100

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBDL*WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92
4	105	100	97	94	104	99	96	93	97	95	92	96	93	91	94	92	90	89
5	103	97	93	91	101	96	93	90	95	92	89	93	91	89	92	90	88	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83
8	95	89	86	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79
10	91	85	82	79	91	85	81	79	84	81	79	84	81	79	83	80	78	78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5002294
5°	4071371
10°	2199270
15°	876883
20°	351609
25°	168372
30°	87276
35°	46135
40°	25568
45°	15838
50°	10899
55°	7311
60°	5624
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P265100

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBDL*WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	661.1	46.7
10°-20°	521.6	36.8
20°-30°	153.9	10.9
30°-40°	51.2	3.6
40°-50°	19.2	1.4
50°-60°	8.5	0.6
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1336.6	94.3
0°-40°	1387.8	97.9
0°-60°	1415.6	99.9
0°-90°	1417.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1417.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10139	
5°	8221	661
15°	1717	522
25°	309	154
35°	77	51
45°	23	19
55°	8	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P265100

CATALOG NUMBER: LD2B20D010 EU2B2010SP159040 2LBDL*WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	10139.2
2.5°	9730.6
5°	8220.9
7.5°	6333.8
10°	4390.0
12.5°	2809.4
15°	1716.8
17.5°	1047.1
20°	669.7
22.5°	448.4
25°	309.3
27.5°	218.5
30°	153.2
32.5°	107.8
35°	76.6
37.5°	53.9
40°	39.7
42.5°	31.2
45°	22.7
47.5°	19.9
50°	14.2
52.5°	11.4
55°	8.5
57.5°	8.5
60°	5.7
62.5°	2.8
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)