

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494656

Luminaire Tested: **LDA2B108030R30D010 2LBDL1MW**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494656
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108030R30D010 2LBDL1MW
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1008.3 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494656
CATALOG NUMBER: LDA2B108030R30D010 2LBDL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P494656

CATALOG NUMBER: LDA2B108030R30D010 2LBDL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	81	78	77
9	90	84	80	77	90	83	80	77	83	79	77	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	75	80	77	75	80	77	74	79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1953959
5°	1863067
10°	1510934
15°	923618
20°	403586
25°	150952
30°	62608
35°	29271
40°	13589
45°	6628
50°	3684
55°	1376
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P494656

CATALOG NUMBER: LDA2B108030R30D010 2LBDL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	335.6	33.3
10°-20°	484.5	48.1
20°-30°	144.6	14.3
30°-40°	33.2	3.3
40°-50°	8.2	0.8
50°-60°	1.9	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	964.7	95.7
0°-40°	997.9	99.0
0°-60°	1008.0	100.0
0°-90°	1008.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1008.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3960	
5°	3762	336
15°	1808	485
25°	277	145
35°	49	33
45°	10	8
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494656

CATALOG NUMBER: LDA2B108030R30D010 2LBDL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	3960.5
1°	3951.6
2°	3911.4
3°	3884.5
4°	3834.3
5°	3761.9
6°	3663.1
7°	3545.3
8°	3395.3
9°	3212.5
10°	3016.0
11°	2805.7
12°	2566.9
13°	2310.2
14°	2066.1
15°	1808.3
16°	1559.0
17°	1313.3
18°	1115.2
19°	922.9
20°	768.7
21°	622.8
22.5°	461.7
23°	416.3
24°	340.7
25°	277.3
26°	227.7
27°	189.7
28°	156.4
29°	131.0
30°	109.9
32.5°	71.8
35°	48.6
37.5°	32.2
40°	21.1
42.5°	13.7
45°	9.5
47.5°	6.9
50°	4.8
52.5°	3.2
55°	1.6
57.5°	1.1
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P494656

CATALOG NUMBER: LDA2B108030R30D010 2LBDL1MW

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)