

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P225413

Luminaire Tested: **LD2B20D010 EU2B20FL409040 2LBDC*MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P225413
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14834)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL409040 2LBDC*MB
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
CAST ROUND TRIM WITH MATTE BLACK FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1577.1 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.6
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P225413

CATALOG NUMBER: LD2B20D010 EU2B20FL409040 2LBDC*MB

Luminous Intensity Polar Plot





TEST NUMBER: P225413

CATALOG NUMBER: LD2B20D010 EU2B20FL409040 2LBDC*MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	103	100	108	104	101	99	101	99	96	98	96	94	96	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83	83	83	83
5	98	91	86	83	96	90	86	82	88	85	82	87	84	81	85	83	80	79	79	79	79
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76	76	76	76
7	91	83	78	75	90	83	78	75	81	77	74	80	77	74	79	76	74	72	72	72	72
8	87	80	75	72	86	79	75	71	78	74	71	77	74	71	76	73	71	69	69	69	69
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67	67	67	67
10	82	74	69	66	81	73	69	66	73	68	65	72	68	65	71	68	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1426944
5°	1402144
10°	1250841
15°	988690
20°	659239
25°	382470
30°	191431
35°	90033
40°	35193
45°	15722
50°	7412
55°	4119
60°	1549
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P225413

CATALOG NUMBER: LD2B20D010 EU2B20FL409040 2LBDC*MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	330.5	21.0
10°-20°	667.4	42.3
20°-30°	419.8	26.6
30°-40°	128.3	8.1
40°-50°	25.2	1.6
50°-60°	5.6	0.4
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1417.7	89.9
0°-40°	1546.0	98.0
0°-60°	1576.8	100.0
0°-90°	1577.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1577.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3684	
5°	3606	331
15°	2466	667
25°	895	420
35°	190	128
45°	29	25
55°	6	6
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P225413

CATALOG NUMBER: LD2B20D010 EU2B20FL409040 2LBDC*MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3683.9
2.5°	3675.7
5°	3606.1
7.5°	3442.3
10°	3180.2
12.5°	2852.5
15°	2465.5
17.5°	2035.5
20°	1599.3
22.5°	1226.6
25°	894.9
27.5°	630.7
30°	428.0
32.5°	288.7
35°	190.4
37.5°	116.7
40°	69.6
42.5°	45.1
45°	28.7
47.5°	18.4
50°	12.3
52.5°	8.2
55°	6.1
57.5°	4.1
60°	2.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)