

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494709

Luminaire Tested: **LDA2B108030R45D010 2LBD1B**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494709
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-40)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108030R45D010 2LBD1B
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1091.9 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.65
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494709
CATALOG NUMBER: LDA2B108030R45D010 2LBD1B

Luminous Intensity Polar Plot





TEST NUMBER: P494709

CATALOG NUMBER: LDA2B108030R45D010 2LBD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95	94	92	91
3	105	100	96	93	104	99	95	92	96	93	90		94	91	89		92	90	88	86
4	101	95	90	87	100	94	90	86	92	88	85		90	87	84		88	86	84	82
5	97	90	86	82	96	90	85	82	88	84	81		86	83	80		85	82	80	78
6	94	86	81	78	92	86	81	77	84	80	77		83	79	76		82	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		78	75	73	71
8	87	79	74	71	86	78	74	70	77	73	70		76	73	70		76	72	70	68
9	84	76	71	67	83	75	70	67	74	70	67		73	70	67		73	69	67	66
10	81	73	68	65	80	72	68	64	71	67	64		71	67	64		70	67	64	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1083719
5°	1067206
10°	995884
15°	869119
20°	664576
25°	385954
30°	163728
35°	67757
40°	29948
45°	15489
50°	7675
55°	1806
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P494709

CATALOG NUMBER: LDA2B108030R45D010 2LBD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	200.5	18.4
10°-20°	464.1	42.5
20°-30°	324.5	29.7
30°-40°	80.3	7.4
40°-50°	18.6	1.7
50°-60°	3.1	0.3
60°-70°	0.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	989.1	90.6
0°-40°	1069.4	97.9
0°-60°	1091.1	99.9
0°-90°	1091.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1091.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2197	
5°	2155	201
15°	1702	464
25°	709	324
35°	112	80
45°	22	19
55°	2	3
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494709

CATALOG NUMBER: LDA2B108030R45D010 2LBD1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	2196.6
1°	2191.9
2°	2190.8
3°	2183.9
4°	2164.4
5°	2154.9
6°	2135.3
7°	2107.3
8°	2073.0
9°	2037.6
10°	1987.9
11°	1947.3
12°	1897.6
13°	1833.1
14°	1767.6
15°	1701.6
16°	1628.7
17°	1542.1
18°	1454.4
19°	1364.0
20°	1265.8
21°	1148.0
22.5°	995.3
23°	932.4
24°	819.4
25°	709.0
26°	605.4
27°	508.7
28°	423.7
29°	349.7
30°	287.4
32.5°	177.0
35°	112.5
37.5°	72.9
40°	46.5
42.5°	31.7
45°	22.2
47.5°	15.8
50°	10.0
52.5°	5.3
55°	2.1
57.5°	1.1
60°	1.1
62.5°	0.5
65°	0.5



TEST NUMBER: P494709

CATALOG NUMBER: LDA2B108030R45D010 2LBD1B

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)