

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494798

Luminaire Tested: **LDA2B108030R70D010 2LBDLC1MB**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494798  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B108030R70D010 2LBDLC1MB  
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1035.9 lumens  
Efficiency: N/A  
Efficacy: 103.6 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494798

CATALOG NUMBER: LDA2B108030R70D010 2LBDLC1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P494798

CATALOG NUMBER: LDA2B108030R70D010 2LBDLC1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85				85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	74	71	67	66				66
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61				61
7	80	70	63	59	78	69	63	58	68	62	58	66	61	58	65	61	57	56				56
8	75	65	58	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52				52
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48				48
10	68	57	51	46	66	57	50	46	56	50	46	55	50	46	54	49	46	45				45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	410132
5°	407736
10°	405036
15°	397529
20°	383163
25°	366793
30°	349445
35°	288313
40°	187415
45°	97960
50°	45515
55°	16687
60°	1677
65°	1284
70°	865
75°	1144
80°	0
85°	0



TEST NUMBER: P494798

CATALOG NUMBER: LDA2B108030R70D010 2LBDLC1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.9	7.5
10°-20°	218.7	21.1
20°-30°	310.4	30.0
30°-40°	290.3	28.0
40°-50°	116.7	11.3
50°-60°	20.4	2.0
60°-70°	1.0	0.1
70°-80°	0.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	607.0	58.6
0°-40°	897.2	86.6
0°-60°	1034.4	99.9
0°-90°	1035.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1035.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	831	
5°	823	78
15°	778	219
25°	674	310
35°	479	290
45°	140	117
55°	19	20
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P494798

CATALOG NUMBER: LDA2B108030R70D010 2LBDLC1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	831.3
1°	832.5
2°	830.7
3°	827.3
4°	825.6
5°	823.3
6°	814.2
7°	817.1
8°	809.1
9°	807.4
10°	808.5
11°	801.1
12°	799.4
13°	790.2
14°	786.8
15°	778.3
16°	773.1
17°	762.8
18°	750.9
19°	744.0
20°	729.8
21°	718.9
22.5°	698.9
23°	693.8
24°	684.1
25°	673.8
26°	665.9
27°	654.4
28°	643.0
29°	629.3
30°	613.4
32.5°	557.4
35°	478.7
37.5°	385.7
40°	291.0
42.5°	207.7
45°	140.4
47.5°	92.4
50°	59.3
52.5°	37.1
55°	19.4
57.5°	6.3
60°	1.7
62.5°	1.1
65°	1.1



TEST NUMBER: P494798

CATALOG NUMBER: LDA2B108030R70D010 2LBDLC1MB

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.6
70°	0.6
72.5°	0.6
75°	0.6
77.5°	0.6
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)