

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224684

Luminaire Tested: **LD2B20D010 EU2B20FL409040 2LBDLC\*MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P224684  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14835)  
Test Lab: INNOVATION CENTER (G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD2B20D010 EU2B20FL409040 2LBDLC\*MW  
Description: 2000 Lumen, 2inch Portfolio LED Downlight  
FLOOD OPTIC  
LENSED CAST ROUND TRIM WITH MATTE WHITE FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1473.0 lumens  
Efficiency: N/A  
Efficacy: 70.5 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.59  
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 20.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P224684

CATALOG NUMBER: LD2B20D010 EU2B20FL409040 2LBDLC\*MW

### Luminous Intensity Polar Plot





TEST NUMBER: P224684

CATALOG NUMBER: LD2B20D010 EU2B20FL409040 2LBDLC\*MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	94	92	91			91
3	105	100	96	93	104	99	95	92	96	93	90	94	91	89	92	90	88	86			86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	85	88	86	84	82			82
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79			79
6	94	86	82	78	93	86	81	78	84	80	77	83	79	77	82	79	76	75			75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	76	73	72			72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69			69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66			66
10	81	73	68	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64			64

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1333516
5°	1309215
10°	1163838
15°	915305
20°	609074
25°	349690
30°	176626
35°	83082
40°	33423
45°	16543
50°	9099
55°	6348
60°	5888
65°	3483
70°	4304
75°	2844
80°	4238
85°	0



TEST NUMBER: P224684

CATALOG NUMBER: LD2B20D010 EU2B20FL409040 2LBDLC\*MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	308.4	20.9
10°-20°	618.3	42.0
20°-30°	384.7	26.1
30°-40°	118.3	8.0
40°-50°	26.0	1.8
50°-60°	9.2	0.6
60°-70°	4.7	0.3
70°-80°	2.8	0.2
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1311.3	89.0
0°-40°	1429.6	97.1
0°-60°	1464.8	99.4
0°-90°	1473.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1473.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3443	
5°	3367	308
15°	2282	618
25°	818	385
35°	176	118
45°	30	26
55°	9	9
65°	4	5
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P224684

CATALOG NUMBER: LD2B20D010 EU2B20FL409040 2LBDLC\*MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3442.7
2.5°	3427.6
5°	3367.1
7.5°	3214.1
10°	2959.0
12.5°	2652.9
15°	2282.5
17.5°	1878.2
20°	1477.6
22.5°	1120.5
25°	818.2
27.5°	576.3
30°	394.9
32.5°	266.4
35°	175.7
37.5°	105.8
40°	66.1
42.5°	45.3
45°	30.2
47.5°	20.8
50°	15.1
52.5°	13.2
55°	9.4
57.5°	7.6
60°	7.6
62.5°	5.7
65°	3.8
67.5°	3.8
70°	3.8
72.5°	3.8
75°	1.9
77.5°	1.9
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)