

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P279460

Luminaire Tested: **LDA2B108035D010 EU2B10FL408035 2LBAD1MW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P279460  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-3)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA2B108035D010 EU2B10FL408035 2LBAD1MW  
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in  
ADJ spun Refl, Self-Flanged, MW  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1175.9 lumens  
Efficiency: N/A  
Efficacy: 117.6 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 10  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P279460

CATALOG NUMBER: LDA2B108035D010 EU2B10FL408035 2LBAD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P279460

CATALOG NUMBER: LDA2B108035D010 EU2B10FL408035 2LBAD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99  | 99  | 98  | 96  |    |    |   |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 100 | 102 | 100 | 98  | 99  | 97  | 96  | 97  | 95  | 94  | 92  |    |    |   |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 98  | 95  | 93  | 96  | 94  | 92  | 94  | 92  | 90  | 89  |    |    |   |
| 4   | 103 | 98  | 93  | 90  | 102 | 97  | 93  | 90  | 95  | 91  | 89  | 93  | 90  | 88  | 91  | 89  | 87  | 85  |    |    |   |
| 5   | 100 | 94  | 89  | 86  | 98  | 93  | 89  | 86  | 91  | 88  | 85  | 90  | 87  | 84  | 88  | 86  | 84  | 82  |    |    |   |
| 6   | 97  | 90  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 82  | 87  | 83  | 81  | 85  | 83  | 80  | 79  |    |    |   |
| 7   | 94  | 87  | 82  | 79  | 92  | 86  | 82  | 79  | 85  | 81  | 78  | 84  | 81  | 78  | 83  | 80  | 78  | 77  |    |    |   |
| 8   | 91  | 84  | 79  | 76  | 90  | 83  | 79  | 76  | 82  | 78  | 76  | 81  | 78  | 75  | 80  | 77  | 75  | 74  |    |    |   |
| 9   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 79  | 76  | 73  | 79  | 75  | 73  | 78  | 75  | 73  | 72  |    |    |   |
| 10  | 85  | 78  | 74  | 71  | 84  | 78  | 74  | 71  | 77  | 73  | 71  | 76  | 73  | 70  | 76  | 72  | 70  | 69  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1617043 |
| 5°  | 1582807 |
| 10° | 1442651 |
| 15° | 1126953 |
| 20° | 667254  |
| 25° | 248067  |
| 30° | 77477   |
| 35° | 34451   |
| 40° | 15972   |
| 45° | 7535    |
| 50° | 4145    |
| 55° | 2322    |
| 60° | 1085    |
| 65° | 584     |
| 70° | 721     |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |



TEST NUMBER: P279460

CATALOG NUMBER: LDA2B108035D010 EU2B10FL408035 2LBAD1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 295.4  | 25.1      |
| 10°-20°   | 587.5  | 50.0      |
| 20°-30°   | 240.6  | 20.5      |
| 30°-40°   | 39.8   | 3.4       |
| 40°-50°   | 9.4    | 0.8       |
| 50°-60°   | 2.5    | 0.2       |
| 60°-70°   | 0.6    | 0.0       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1123.6 | 95.5      |
| 0°-40°    | 1163.4 | 98.9      |
| 0°-60°    | 1175.3 | 99.9      |
| 0°-90°    | 1175.9 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1175.9 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3278 |      |
| 5°  | 3196 | 295  |
| 15° | 2206 | 588  |
| 25° | 456  | 241  |
| 35° | 57   | 40   |
| 45° | 11   | 9    |
| 55° | 3    | 3    |
| 65° | 0    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P279460

CATALOG NUMBER: LDA2B108035D010 EU2B10FL408035 2LBAD1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3277.6 |
| 1°    | 3266.2 |
| 2°    | 3251.1 |
| 3°    | 3237.6 |
| 4°    | 3219.8 |
| 5°    | 3196.0 |
| 6°    | 3160.9 |
| 7°    | 3115.1 |
| 8°    | 3049.7 |
| 9°    | 2970.4 |
| 10°   | 2879.7 |
| 11°   | 2774.4 |
| 12°   | 2655.6 |
| 13°   | 2520.1 |
| 14°   | 2369.5 |
| 15°   | 2206.4 |
| 17.5° | 1749.7 |
| 20°   | 1270.9 |
| 22.5° | 813.6  |
| 25°   | 455.7  |
| 27.5° | 240.2  |
| 30°   | 136.0  |
| 32.5° | 86.4   |
| 35°   | 57.2   |
| 37.5° | 37.8   |
| 40°   | 24.8   |
| 42.5° | 16.2   |
| 45°   | 10.8   |
| 47.5° | 7.6    |
| 50°   | 5.4    |
| 52.5° | 3.8    |
| 55°   | 2.7    |
| 57.5° | 1.6    |
| 60°   | 1.1    |
| 62.5° | 0.5    |
| 65°   | 0.5    |
| 67.5° | 0.5    |
| 70°   | 0.5    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |



TEST NUMBER: P279460

CATALOG NUMBER: LDA2B108035D010 EU2B10FL408035 2LBAD1MW

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







|       |  |     |
|-------|--|-----|
| 85°   |  | 0.0 |
| 87.5° |  | 0.0 |



(END OF REPORT)