

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280357

Luminaire Tested: **LDA2B108035D010 EU2B10WFL558035 2LBAD1B**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108035D010 EU2B10WFL558035 2LBAD1B
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl, Self-Flanged, B
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1160.5 lumens
Efficiency: N/A
Efficacy: 116.0 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280357

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBAD1B

Luminous Intensity Polar Plot





TEST NUMBER: P280357

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBAD1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95			
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90			
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85			
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80			
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76			
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72			
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69			
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65			
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62			
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	991065
5°	970881
10°	902853
15°	788316
20°	652658
25°	499182
30°	273164
35°	101123
40°	35036
45°	15768
50°	7445
55°	3699
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P280357

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBAD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.2	15.7
10°-20°	426.6	36.8
20°-30°	403.2	34.7
30°-40°	124.1	10.7
40°-50°	19.6	1.7
50°-60°	4.2	0.4
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1011.9	87.2
0°-40°	1136.1	97.9
0°-60°	1159.8	99.9
0°-90°	1160.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1160.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2009	
5°	1960	182
15°	1543	427
25°	917	403
35°	168	124
45°	23	20
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280357

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBAD1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	2008.8
1°	2001.3
2°	1992.2
3°	1984.6
4°	1974.9
5°	1960.4
6°	1941.6
7°	1916.3
8°	1882.4
9°	1843.1
10°	1802.2
11°	1757.0
12°	1709.1
13°	1656.9
14°	1602.6
15°	1543.4
17.5°	1386.8
20°	1243.1
22.5°	1097.2
25°	917.0
27.5°	699.6
30°	479.5
32.5°	294.4
35°	167.9
37.5°	93.6
40°	54.4
42.5°	33.9
45°	22.6
47.5°	15.1
50°	9.7
52.5°	6.5
55°	4.3
57.5°	2.7
60°	1.1
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280357

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBAD1B

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)