

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P280368

Luminaire Tested: **LDA2B108035D010 EU2B10WFL558035 2LBALD1WHH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P280368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-5)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B108035D010 EU2B10WFL558035 2LBALD1WHH
Description: PORTFOLIO 2IN ADJ 1000 LUMEN LED LUMINAIRE WITH WIDE FLOOD OPTIC AND
2in ADJ spun Refl w/lens Self-Flanged, WHH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1157.9 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.73
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P280368

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBALD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P280368

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBALD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	99	98	97	97	95
2	109	105	101	98	107	103	100	97	100	98	95	97	95	93	95	93	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76
6	92	84	79	75	91	84	79	75	82	78	75	81	77	74	80	76	74	72
7	88	80	75	71	87	80	75	71	78	74	71	77	73	70	76	73	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65
9	81	73	68	64	80	72	68	64	72	67	64	71	67	64	70	66	64	62
10	78	70	65	61	77	69	64	61	69	64	61	68	64	61	67	63	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	988894
5°	968751
10°	900849
15°	786579
20°	651188
25°	498094
30°	272537
35°	100882
40°	34907
45°	15768
50°	7445
55°	3699
60°	1085
65°	584
70°	721
75°	0
80°	0
85°	0



TEST NUMBER: P280368

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBALD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.8	15.7
10°-20°	425.6	36.8
20°-30°	402.3	34.7
30°-40°	123.8	10.7
40°-50°	19.6	1.7
50°-60°	4.1	0.4
60°-70°	0.6	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1009.7	87.2
0°-40°	1133.5	97.9
0°-60°	1157.2	99.9
0°-90°	1157.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1157.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2004	
5°	1956	182
15°	1540	426
25°	915	402
35°	168	124
45°	23	20
55°	4	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P280368

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBALD1WHH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2004.4
1°	1996.9
2°	1987.8
3°	1980.3
4°	1970.6
5°	1956.1
6°	1937.3
7°	1912.1
8°	1878.2
9°	1839.0
10°	1798.2
11°	1753.1
12°	1705.3
13°	1653.3
14°	1599.0
15°	1540.0
17.5°	1383.7
20°	1240.3
22.5°	1094.8
25°	915.0
27.5°	698.0
30°	478.4
32.5°	293.7
35°	167.5
37.5°	93.4
40°	54.2
42.5°	33.8
45°	22.6
47.5°	15.0
50°	9.7
52.5°	6.4
55°	4.3
57.5°	2.7
60°	1.1
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P280368

CATALOG NUMBER: LDA2B108035D010 EU2B10WFL558035 2LBALD1WHH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)