

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494818

Luminaire Tested: **LDA2B108035R20D010 2LBD1WHH**

Issue Date: 3/8/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494818
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-1)
Test Lab: INNOVATION CENTER
Issue Date: 3/8/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108035R20D010 2LBD1WHH
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1095.4 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494818

CATALOG NUMBER: LDA2B108035R20D010 2LBD1WHH

Luminous Intensity Polar Plot





TEST NUMBER: P494818

CATALOG NUMBER: LDA2B108035R20D010 2LBD1WHH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10							
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10				
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	111	106	106	106	106	102	102	102	102	100	100	100	100
1	116	114	112	110	113	111	110	109	108	106	105	105	104	103	102	102	101	100	99	99	98	98	98	98
2	112	109	106	104	110	107	105	103	104	102	101	101	102	100	99	99	99	98	97	97	97	96	95	95
3	109	105	102	100	108	104	101	99	102	99	97	97	99	97	96	96	97	96	94	94	94	93	92	92
4	107	102	99	96	105	101	98	95	99	96	94	94	97	95	93	93	96	94	92	92	92	91	90	90
5	104	99	95	93	103	98	95	92	97	94	92	92	95	93	91	91	94	92	90	90	90	89	88	88
6	102	96	93	90	101	96	92	90	95	92	89	89	93	91	89	89	92	90	88	88	88	87	86	86
7	100	94	91	88	99	94	90	88	92	90	87	87	92	89	87	87	91	88	87	87	87	86	85	85
8	98	92	88	86	97	91	88	86	91	88	86	86	90	87	85	85	89	87	85	85	85	84	83	83
9	96	90	87	84	95	90	86	84	89	86	84	84	88	86	84	84	88	85	83	83	83	82	81	81
10	94	88	85	83	93	88	85	82	87	84	82	82	87	84	82	82	86	84	82	82	82	81	80	80

AVERAGE LUMINANCE (cd/sqm):

0°	
0°	4060170
5°	3382879
10°	1983952
15°	694897
20°	233898
25°	90147
30°	41359
35°	18309
40°	8952
45°	5233
50°	2840
55°	946
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P494818

CATALOG NUMBER: LDA2B108035R20D010 2LBD1WHH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	558.9	51.0
10°-20°	419.6	38.3
20°-30°	88.2	8.0
30°-40°	21.1	1.9
40°-50°	6.0	0.6
50°-60°	1.3	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1066.7	97.4
0°-40°	1087.8	99.3
0°-60°	1095.1	100.0
0°-90°	1095.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1095.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8230	
5°	6831	559
15°	1360	420
25°	166	88
35°	30	21
45°	8	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494818

CATALOG NUMBER: LDA2B108035R20D010 2LBD1WHH

CANDELA DISTRIBUTION (FULL):

0°	
0°	8229.6
1°	8129.2
2°	7883.5
3°	7600.4
4°	7283.6
5°	6830.7
6°	6349.9
7°	5816.3
8°	5206.9
9°	4591.5
10°	3960.2
11°	3310.6
12°	2738.6
13°	2180.4
14°	1735.4
15°	1360.5
16°	1067.2
17°	841.8
18°	676.8
19°	548.6
20°	445.5
22.5°	270.3
25°	165.6
27.5°	108.4
30°	72.6
32.5°	44.3
35°	30.4
37.5°	20.8
40°	13.9
42.5°	10.1
45°	7.5
47.5°	5.3
50°	3.7
52.5°	2.1
55°	1.1
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0



TEST NUMBER: P494818

CATALOG NUMBER: LDA2B108035R20D010 2LBD1WHH

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)