

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494867

Luminaire Tested: **LDA2B108035R30D010 2LBDL1GPH**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P494867
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-16)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LDA2B108035R30D010 2LBDL1GPH
Description: 1000 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 80 CRI LEDS AND 3500K CCT LEDS
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1019.4 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 10
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P494867

CATALOG NUMBER: LDA2B108035R30D010 2LBDL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P494867

CATALOG NUMBER: LDA2B108035R30D010 2LBDL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	92	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	91	89	86	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	95	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	81	78	77
9	90	84	80	77	90	83	80	77	83	79	77	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	75	80	77	75	80	77	74	79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1975667
5°	1883769
10°	1527666
15°	933884
20°	408049
25°	152640
30°	63292
35°	29572
40°	13782
45°	6698
50°	3684
55°	1376
60°	493
65°	584
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P494867

CATALOG NUMBER: LDA2B108035R30D010 2LBDL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	339.3	33.3
10°-20°	489.9	48.1
20°-30°	146.2	14.3
30°-40°	33.6	3.3
40°-50°	8.3	0.8
50°-60°	1.9	0.2
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	975.4	95.7
0°-40°	1009.0	99.0
0°-60°	1019.1	100.0
0°-90°	1019.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1019.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4004	
5°	3804	339
15°	1828	490
25°	280	146
35°	49	34
45°	10	8
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494867

CATALOG NUMBER: LDA2B108035R30D010 2LBDL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4004.5
1°	3995.4
2°	3954.8
3°	3927.6
4°	3876.8
5°	3803.7
6°	3703.8
7°	3584.7
8°	3433.0
9°	3248.1
10°	3049.4
11°	2836.8
12°	2595.4
13°	2335.8
14°	2089.0
15°	1828.4
16°	1576.3
17°	1327.9
18°	1127.6
19°	933.2
20°	777.2
21°	629.8
22.5°	466.8
23°	420.9
24°	344.5
25°	280.4
26°	230.2
27°	191.8
28°	158.1
29°	132.5
30°	111.1
32.5°	72.6
35°	49.1
37.5°	32.6
40°	21.4
42.5°	13.9
45°	9.6
47.5°	6.9
50°	4.8
52.5°	3.2
55°	1.6
57.5°	1.1
60°	0.5
62.5°	0.5
65°	0.5



TEST NUMBER: P494867

CATALOG NUMBER: LDA2B108035R30D010 2LBDL1GPH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)