

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P224469

Luminaire Tested: **LD2B20D010 EU2B20FL408050 2LBDL*WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P224469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14831)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD2B20D010 EU2B20FL408050 2LBDL*WH
Description: 2000 Lumen, 2inch Portfolio LED Downlight
FLOOD OPTIC
LENSED SPUN ROUND TRIM WITH WHEAT HAZE FINISH
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1867.2 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.59
Luminous Opening: Rectangular (W 0.17' x L: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 20.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P224469

CATALOG NUMBER: LD2B20D010 EU2B20FL408050 2LBDL*WH

Luminous Intensity Polar Plot





TEST NUMBER: P224469

CATALOG NUMBER: LD2B20D010 EU2B20FL408050 2LBDL*WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95				95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91				91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87				87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82				82
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79				79
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75				75
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72				72
8	87	79	75	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69				69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66				66
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64				64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1722837
5°	1657641
10°	1459065
15°	1146047
20°	779191
25°	454998
30°	231730
35°	109657
40°	47834
45°	20761
50°	10003
55°	6416
60°	3641
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P224469

CATALOG NUMBER: LD2B20D010 EU2B20FL408050 2LBDL*WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	389.4	20.9
10°-20°	777.1	41.6
20°-30°	498.8	26.7
30°-40°	158.3	8.5
40°-50°	33.8	1.8
50°-60°	8.7	0.5
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1665.3	89.2
0°-40°	1823.6	97.7
0°-60°	1866.1	99.9
0°-90°	1867.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1867.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4448	
5°	4263	389
15°	2858	777
25°	1065	499
35°	232	158
45°	38	34
55°	10	9
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P224469

CATALOG NUMBER: LD2B20D010 EU2B20FL408050 2LBDL*WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4447.8
2.5°	4405.2
5°	4263.2
7.5°	4031.4
10°	3709.6
12.5°	3316.9
15°	2857.9
17.5°	2368.2
20°	1890.3
22.5°	1443.2
25°	1064.6
27.5°	759.4
30°	518.1
32.5°	347.8
35°	231.9
37.5°	153.8
40°	94.6
42.5°	59.1
45°	37.9
47.5°	26.0
50°	16.6
52.5°	11.8
55°	9.5
57.5°	7.1
60°	4.7
62.5°	2.4
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)